


Blades



493785

|          |                                                                                                                                           | Price Each |
|----------|-------------------------------------------------------------------------------------------------------------------------------------------|------------|
| Blades   | Description                                                                                                                               | Order Code |
| S60      | Heavy duty HSS blade for heavy duty internal deburring in difficult to reach places                                                       | 137-4069   |
| S101     | Extra fine point HSS blade used for steel and aluminium                                                                                   | 137-4080   |
| S202     | Extra fine point HSS blade used for brass and cast iron. For both left and right handed use                                               | 137-4081   |
| S150     | HSS blade for 0.75mm radius or larger, holes 1.5mm diameter or larger                                                                     | 137-4098   |
| BC3200   | 3.2mm countersink blade. For use with the NB handle and/or SN holder                                                                      | 137-4099   |
| C12      | 90 , 12mm countersink for use with the C holder                                                                                           | 137-4055   |
| C20      | 90 , 20mm countersink for use with the C holder                                                                                           | 137-4056   |
| C30      | 90 , 30mm countersink for use with the C holder                                                                                           | 137-4057   |
| BC6300   | Single flute, 6.3mm countersink. For use with NB handle and/or SN holder                                                                  | 137-4100   |
| BC8300   | Single flute, 8.3mm countersink. For use with NB handle and/or SN holder                                                                  | 137-4101   |
| BC1040   | Single flute, 10.4mm countersink. For use with NB handle and/or SN holder                                                                 | 137-4103   |
| T80      | 4mm triangular section x 85mm long Scraper Blade, ground both ends for prolonged life. For use with the Adjustable Scraper Handle only    | 720-0468   |
| T120     | 7mm triangular section x 120mm long Scraper Blade, ground both ends for prolonged life. For use with the Uni Handle only                  | 137-4049   |
| D50      | HSS 3mm Mini Scraper Blade. Most suitable for miniature components                                                                        | 137-4058   |
| D66      | HSS 3.2mm Internal Scraper Blade. Most useful on cross holes                                                                              | 137-4109   |
| N80      | Used in the Double Burr, cutting along the circumference of each face                                                                     | 137-4070   |
| N80 M42  | Used in the Double Burr, cutting along the circumference of each face. The N80 M42 blade is used for stainless steel                      | 137-4105   |
| N80K M42 | Similar to the N80 but ground as shown, to facilitate use in narrow keyways. The N80K M42 Blade is used on stainless steel (2.5mm - 11mm) | 137-4106   |
| N70K     | Square Blade for shallow keyways 1.2mm - 8mm)                                                                                             | 137-4107   |
|          | Heavy duty blade for wide keyways                                                                                                         |            |

|      |                                                   |          |
|------|---------------------------------------------------|----------|
| N90K | 1.2mm - 6mm                                       | 137-4107 |
| N90K | Heavy duty blade for wide keyways<br>(3mm - 15mm) | 137-4108 |