

**TIGER™
EYE
SYSTEM**

Diagram illustrating four different SMM connector types:

- SMM-135-02-L-D-K
- SMM-108-02-L-S
- SMM-115-02-S-D
- SMM-110-02-L-S

SMM SERIES

TIGER EYE™ SOCKET STRIP

10 YEAR MFG
WITH 30 μ m GOLD

**EXTENDED LIFE
PRODUCT**

HIGH MATING
CYCLES



**TIGER™
EYE**
CONTACT

8
G b p s

UL[®]
FILE NO. E111594

SMM	1	NO. PINS PER ROW	02	PLATING OPTION	ROW OPTION	OTHER OPTION
02 thru 40				–F = Gold flash on contact, Matte Tin on tail –L = 10 μ" (0.25 μm) Gold on contact, Matte Tin on tail –S = 30 μ" (0.76 μm) Gold on contact, Matte Tin on tail	–S = Single Row –D = Double Row	–“XX” = Polarized Position –K = (5.50 mm) .217" DIA Polyimide Film Pick & Place Pad (2 positions minimum, –02 thru –05 requires –TR) –P = Plastic Pick & Place Pad (–02 thru –05 requires –TR) –TR = Tape & Reel Packaging (27 positions maximum)

*All parts within this catalog are built to Samtec's specifications.
Customer specific requirements must be approved by Samtec and identified in a Samtec customer-specific drawing to apply.*