

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [0391001012](#)  
**Status:** **Active**  
**Description:** 10.00mm (.394") Pitch Beau™ Eurostyle™ Two-Screw Terminal Strips, 12 Circuits

**Documents:**

[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Drawing \(PDF\)](#)

**General**

|                             |                       |
|-----------------------------|-----------------------|
| Product Family              | Terminal Blocks       |
| Series                      | <a href="#">39100</a> |
| Application                 | Wire-to-Wire          |
| Component Type              | One Piece             |
| Product Literature Order No | USA-303               |
| Product Name                | Eurostyle™Two Screw   |
| Type                        | Euro Block            |

**Physical**

|                               |                                |
|-------------------------------|--------------------------------|
| Circuits (Loaded)             | 12                             |
| Entry Angle                   | Horizontal                     |
| Lock to Mating Part           | None                           |
| Number of Rows                | 2                              |
| Orientation                   | Vertical                       |
| PCB Retention                 | Yes                            |
| Panel Mount                   | Mounting Holes Between Circuit |
| Pitch - Mating Interface (in) | 0.394 In                       |
| Pitch - Mating Interface (mm) | 10.00 mm                       |
| Pitch - Term. Interface (in)  | 0.315 In                       |
| Pitch - Term. Interface (mm)  | 8.00 mm                        |
| Polarized to Mating Part      | No                             |
| Stackable                     | No                             |
| Temperature Range - Operating | 100°C                          |
| Wire Size AWG                 | 10, 12, 14, 16, 18             |


**Electrical**

|                   |      |
|-------------------|------|
| Current - Maximum | 30A  |
| Voltage - Maximum | 600V |

**Material Info**

**Reference - Drawing Numbers**

|               |              |
|---------------|--------------|
| Sales Drawing | SD-39100-004 |
|---------------|--------------|



*Series*  
*image - Reference only*

**EU RoHS**

**ELV and RoHS**  
**Compliant**  
**REACH SVHC**  
Not Reviewed  
**Halogen-Free**  
**Status**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**  
[39100Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION