



VERSATILE

- Multiple power options – rechargeable AA NiMH, AA Lithium, AA Alkaline
- Recharge NiMH batteries with included car charger or wall adaptor



TOUGH

- Survives a 2-meter drop test
- Shatterproof lens



BRIGHT

- Provides 110 lumens
- Intense, focused beam



POWERFUL

- Illuminates objects up to 385 meters away
- Tight white spot is ideal for search applications



634497

European Region

The Energizer® Hard Case Rechargeable Spotlight offers a wealth of power options. It uses 4 AA batteries and can charge NiMH batteries using the included wall adaptor or car charger. It stands up to rough treatment and provides an intense focused beam that illuminates objects up to 385 meters away.




230 mm

Before Using Your Flashlight:
Please read all instructions and cautionary markings on the package and light

European Region Product Detail:

Designation: Energizer
Hard Case Rechargeable Spotlight
SAP: 634497
Colour: Black and Dark Grey
Power Source: Four "AA" Li, Alkaline or NiMH;
on-board NiMH battery pack
IEC: LR6, FR6, 1.2H2
Lamp: High Output White LED
Lamp Life (hr): Lifetime
Lamp Output (lumens): 110
Beam Distance (m): 385
Peak Beam Intensity (cd): 37 000
Run Time (h:mm): 8:15 Li, 4:00 hrs NiMH, 2:30 Alk
Typical Weight: 7725 grams
without replaceable batteries
Dimensions (mm): 230 x 108

Performance:



Tested according to ANSI/NEMA FL 1 Standards.

Important Notice

This datasheet contains information specific to products manufactured at the time of its publication
Contents herein do not constitute a warranty
©Energizer / All Rights Reserved