

Search within category

GO

BUY NOW

DESIGN / INSTALL



HB1B1F0BA06J1

The 20A, 208V horizontal power strip in black has six NEMA L6-20R receptacles. It features a red LED current monitor and a 10' (3m) power cord with a NEMA L6-20P twist-lock plug. It is UL and c-UL listed and measures 3.4H x 17.0W x 6.0D (86mm x 431mm x 155mm). It takes up two rack spaces and is sold individually.

Specs

Packaging Details

Documents

★ Add to Favorites

Add to BOM

Rack PDU Type	Basic Rack PDU with Local Meter
Monitoring	Local Meter
Remote Outlet Switching	No
Mount Orientation	Horizontal
Current Rating (Amps)	20A
Input Voltage	208V - Single Phase
Plug Type	NEMA L6-20P
Output Voltage	208V
Receptacle Type	NEMA L6-20R
Total Number of Outlets	6
Depth (In.)	6.00
Depth (mm)	152.4
Height (In.)	3.39
Height (mm)	86.1
Width (In.)	17.00
Width (mm)	431.8
Tool-Less Button Spacing (In.)	NA
Tool-Less Button Spacing (mm)	NA
No. of Rack Spaces	2
Surge Suppression	No
Amps	20A
Cable Length	3
Length (In.)	22.50
UL Recognized	Yes
Voltage	208V
RoHS Compliancy Status	Compliant
Min. Order Qty.	1