

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0906471106
Status: Obsolete
Description: 2.5mm UF Hdr WtB Vt Ltc SPeg Red 6Ckt

Documents:
[Drawing \(PDF\)](#)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	PCB Headers
Series	90647
Application	Signal

Physical

Breakaway	No
Circuits (Loaded)	6
Circuits (maximum)	6
Color - Resin	Natural
Durability (mating cycles max)	15
Flammability	94V-0
Glow-Wire Compliant	No
Material - Metal	Brass
Material - Plating Termination	90/10 Tin Lead, 90/10 Tin-Lead
Material - Resin	Polyester
Number of Rows	1
PC Tail Length	2.50mm (.098")
PCB Locator	Yes
PCB Thickness - Recommended	1.50mm (.059"), 1.60mm (.063")
Pitch - Mating Interface	2.50mm (.098")
Pitch - Termination Interface	2.50mm (.098")
Plating min - Mating	5.080µm (200µ")
Plating min - Termination	5.080µm (200µ")
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Closed Ends
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-25°C to +85°C
Termination Interface: Style	Through Hole

Electrical

Current - Maximum per Contact	3A
Voltage - Maximum	250V DC

Material Info

Reference - Drawing Numbers

Product Specification	PS-99020-0018
Sales Drawing	SDA-90647

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
90647Series