


Item # REG24PTP1LHU, TEMP CTRL, 24X48, PT100, 1 SSR, MODBUS

*Note that images may not be exact representation of part number.



SPECIFICATIONS

Size	24x48 (1/32 DIN)
Input Type	Thermocouple PT100 Probe
Supply Voltage	100/240 VAC
Output Type	1 solid state relay
Relay outputs	24 VDC, 20 mA, 850 ohms
Alarms	No
Maximum Consumption	6-100 VA 8-240 VA
Communication on Modbus bus	No
Functions Available	Hysteresis PID Auto-tuning Fuzzy logic
Ramps	8 steps
Operating Mode	Automatic
Display	0.5% FS
Response Time	500 ms

Max Number of Recording Operations to Memory (EEPROM)	100000
Operating Temperature Range	-10 to +50 °C
Storage Temperature Range	-20 to +60 °C
Relative Humidity	90% without condensation
Altitude	Operation: 2000 m Storage: 3000 m
Vibration Resistance - Operational	1 gn (10-70 Hz)
Shock Resistance	5 g-n
Weight	200 G
Degree of Protection	IP66 NEMA 4X
Approvals	CE CSA C22.2 n° 24-93 cURus (873) GOST

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[REG24PTP1LHU](#)