

[All Categories](#) > [Control Components](#) > [Counters](#) > [Preset Counters](#) > [H7CX-N](#) > Item # H7CX-A4SD-N DC12-24

Item # H7CX-A4SD-N DC12-24, 5 kHz Counting Speed [Max] Counter

Request Information

[Printable Page](#)

[Download PDF](#)

[Email This Page](#)



Screw Term,Tr. out, 4-digits

Specifications

Type	Counter
Display Type	Backlight Liquid Crystal Display (LCD)
Accessories	Y92P-CXC4G, Y92P-CXC4S, Y92P-CXC4B, Y92A-48F1, Y92A-48
Preset Counter	Yes
Totalizer	Yes
Operation	1-Stage Preset Counter, Total and Preset Counter
Counting Method	Up/Down Reversible, Command Input, Individual input, Quadrature input
Count Input Type	No-voltage input/voltage input (selectable)
Display Digits	4
Terminal Type	Screw Terminal
Range	-999, 9999
Output Type	Transistor (Single Pole Single Throw (Single Pole Single Throw (SPST)))
Cut Out Size	48x48 mm 1/16 DIN
Mounting	Flush Mounting
Counting Speed [Max]	5 kHz
Direct Current (DC) Supply Voltage	12 to 24 V

News

[Product News](#)

[Corporate News](#)

[Omron on Social Media](#)
[eNews](#)

Company Info

[About Omron](#)

[Omron Principles](#)

[Company Profile](#)

[Business Fields](#)

[Events](#)

[Giving Back](#)

[Environmental](#)

Careers

[Awards](#)

[Giving Back](#)

[Summer Internships](#)

Contact

[Omron in United States](#)

[Contact Us](#)

[Global presence](#)

Follow us



[Facebook](#)



[Twitter](#)



[LinkedIn](#)



[Youtube](#)

[Omron Americas](#) [Omron Corporation](#) [Legal Notices](#) [Privacy Policy](#) [Sitemap](#)

Copyright © Omron Corporation 2017. All rights reserved.
