



THE DRAWING ON THIS PRINT AND INFORMATION THEREWITH ARE PROPRIETARY TO VARI-TRONIX AND SHALL NOT BE USED IN WHOLE OR IN PART WITHOUT WRITTEN PERMISSION OF VARI-TRONIX.



ISSUE	AMENDMENT	DATE



DOT SIZE FOR CUSTOMER REFERENCE ONLY

DISPLAY TYPE	3.5" TFT, +VE, TRANSMISSIVE, 16M COLORS
DISPLAY RESOLUTION	320 X RGB X 240 DOTS
VIEWING ANGLE	6.0° CLOCK
MUX RATIO AND BIAS RATIO	1/240 DUTY
LCD CONTROLLER/DRIVER	HX8216-A, HX8615-A
LOGIC VOLTAGE	3.3V
LCD DRIVING VOLTAGE	TBD
OPERATION TEMPERATURE	-20°C to +70°C
STORAGE TEMPERATURE	-30°C to +80°C
TYPE	LHD02
COLOR	WHITE (USE 6 LEDs)
WAVELENGTH	TBD
DRIVING VOLTAGE	-9.6V
LUMINANCE(CD/M2)	TBD
CONTRAST RATIO	5000 cd/m²
REMARKS	TBD

TITLE: LCM MODULE SPECIFICATION

PROJECT NO: COG-T350MCQA-01

CUSTOMER REF:

TOLERANCE UNLESS OTHERWISE SPECIFIED:	X.X ±0.3
DIMENSIONS IN MM	X.XX ±0.1
ANGULAR ± 1°	

MATERIAL: N/A

FINISH: N/A

SCALE: DO NOT IN SCALE OVERALL THK: N/A

THIRD ANGLE PROJECTION

NAME	SIGN	DATE
DRAWN: ZH TAN		06.04.14
CHECKED: DENG JUN		
APPROVED: ALFRED CHAN		

ITEM NO.: COG-T350MCQA-01

DESCRIPTION: COG-T350MCQA-01

FILE NO: COG-T350MCQA-01 REV: 0

SHEET 1 OF 1

PIN ASSIGNMENT:

1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17
VCC	NC	NC	NC	NC	NC	NC	NC	NC	NC	NC	NC	NC	NC	NC	NC	NC
D18	D14	D15	D16	D17	D20	D21	D22	D23	D24	D25	D26	D27	D28	D29	D30	D31

NOTES:

1. SPECIAL CHARACTERISTIC
2. + SAFETY CHARACTERISTIC
3. * CRITICAL DIMENSION
4. (.) REFERENCE DIMENSION

Mouser Electronics

Related Product Links

[825-COG-T350MCQA-01 - Varitronix COG-T350MCQA-01](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Varitronix:](#)

[COG-T350MCQA-01](#)