

Technical Specs

Feature	Product Features
---------	------------------

Projector

Projector brightness	20ANSI lumens
Projection technology	DLP
Native resolution	WVGA (854x480)
Contrast ratio (typical)	2000:1
Projection distance	0.25 - 3.2m
Aspect ratio	16:9
Number of colours	16.7M
Throw ratio	41"@2m
Zoom ratio	-
Screen size compatibility	~"

Lamps

Service life of lamp	-h
Lamp power	-W
Lamp type	LED
Service life of lamp (economic mode)	20000h

Lens System

Focal length	-mm
--------------	-----

Scanning Frequency

Vertical scan range	50 - 60Hz
Horizontal scan range	30 - 50kHz

Video

Signal format system	-
----------------------	---

Audio

Speakers	1 x 0.5W
Built-in speakers	Yes

Connectivity

DVI port	No
Ethernet LAN (RJ-45) ports quantity	-
RS-232 ports	-
HDMI ports quantity	1
Component video (YPbPr/YCbCr) in	1
Composite video in	Yes
USB 2.0 ports quantity	1
Audio (L,R) in	-
S-Video in	-
RGB ports quantity	-

Technical Details

Handheld remote control	No
Source data-sheet	ICEcat.biz

Weight & Dimensions

Dimensions W x D x H	118 x 60.8 x 18.6mm
Weight	166g

Energy Management

Power consumption	7.9W
Power consumption (standby)	1W

Sound Emission

Noise level	-dB
-------------	-----

Storage Media

Compatible memory cards	SDHC
-------------------------	------

Networking

Feature	Product Features
Ethernet LAN connection	No
Wireless LAN (WLAN) connection	No

Storage Media
