

FLKM 14-PA-AB/1756/IN/EXTC

Order No.: 2302874

The illustration shows the version FLKM 50-PA-AB/1756/IN/EXTC



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2302874>

VARIOFACE front adapter, for Allen Bradley ControlLogix and Honeywell PlantScape, input card IA 16, IB 16, IC 16, IN 16. The front adapters are pushed into the high 1756-TBE hoods (not supplied as standard).

Commercial data

GTIN (EAN)	 4 017918 917531
Note	Made-to-order
sales group	I603
Pack	1 pcs.
Customs tariff	85369010
Catalog page information	Page 190 (IF-2009)

Product notes

WEEE/RoHS-compliant since:
07/11/2006



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

General

Nominal voltage U_N	< 50 V AC
	60 V DC
Channels which can be connected	16

Connection type, plug connector	Flat-ribbon cable plug connector in acc. with IEC 60603-13
Number of plug connectors	2
No. of positions, plug connector	14
Number of positions	14
Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Mounting position	Any
Standards/regulations	IEC 60664
	DIN EN 50178
	IEC 62103
Max. permissible current	1 A (per path)
Pollution degree	2
Surge voltage category	II
Supported controller	ALLEN-BRADLEY ControlLogix
Supported I/O card	1756-IN16
	1756-IA16
	1756-IB16
	1756-IC16
Supported controller	HONEYWELL PlantScape
Supported I/O card	TC-IDA 161

Certificates / Approvals




Certification

CUL, UL

Diagrams/Drawings

Circuit diagram



Connection scheme: FLKM 14-PA-AB/1756/IN/EXTC

Address

PHOENIX CONTACT Deutschland GmbH
Flachsmarktstr. 8
32825 Blomberg, Germany
Phone +49 5235 3 12000
Fax +49 5235 3 41200
<http://www.phoenixcontact.de>



© 2011 Phoenix Contact
Technical modifications reserved;