


8 7 6 5 4 3 2 1

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


RoHS Compliant

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	1/25/10	D.GRIFFIN
B	ECN 5868: ADDED LENGTH 075 M, REVISED 03M TO .98	12/7/11	D.FRISIELLO
C	ECN 6320: ADDED NEW L-COM LOGO	8/3/12	D.FRISIELLO
D	ECN6237: ADDED CONTACT PLATING NOTE. UPDATED FORMAT.	09/14/12	DFP



- NOTES:
1. CABLE ASSEMBLY SHALL HAVE 360Å SHIELD TERMINATION.
 2. CABLE ASSEMBLY SHALL MEET USB 2.0 REQUIREMENTS.
 3. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 4. MOUNTING HARDWARE INCLUDED: 2X #4-40 X .38 LG. PHILLIPS HD SCREW
 5. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

MODEL NUMBER	LENGTH METERS [FEET]
UPMAB-03M	0.3 [.98]
UPMAB-05M	0.5 [1.64]
UPMAB-075M	0.75 [2.46]
UPMAB-1M	1.0 [3.28]
UPMAB-2M	2.0 [6.56]
UPMAB-3M	3.0 [9.84]
UPMAB-4M	4.0 [13.12]
UPMAB-5M	5.0 [16.41]

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]		APPROVALS		DATE		 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845			
OVERALL CABLE LENGTH TOLERANCE: 012 [305] = +1 [25] / -0 >12 [305] 060 [1524] = +2 [51] / -0 >60 [1524] 0120 [3048] = +4 [102] / -0 >120 [3048] 0300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%		DRAWN BY D. PARHAM		01/04/2010					
ALL OTHER DIMENSIONAL TOLERANCES: .X = 0.2 .XX = 0.02 .XXX = 0.005		CHECKED BY D. CASTRO		01/12/2010					
PROJECTION 		APPROVED BY S. SMITH		01/13/2010					
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		CATEGORY		USB					
COLOR VARIATIONS MAY OCCUR		PRODUCT DESCRIPTION		CA USB-A PNL/USB-BM					
SIZE A		FSCM NO. 43321		DWG. NO. UPMAB		REV. D			
SCALE: NONE		CAD FILE: UPMAB.SLDDRW		SHEET 1 OF 1					