

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1210120047](#)
Status: **Active**
Overview: [mPm DIN Valve Connectors](#)
Description: mPm DIN Base, Form B-11mm, B22 Base, 2 Pole Plus Ground Terminal, 250V AC/300V DC, Black, Nitrile Gasket with Screws

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Packaging Specification PK-121013-B22-001 \(PDF\)](#)

General
Product Family Field Attachable / Accessories
Series [121012](#)
Form B - 11mm
IP Rating IP65, IP67
Material - Contact Brass
Overview [mPm DIN Valve Connectors](#)
Product Name mPm
Type Field Attachable Connector
UPC 883906317294

Physical
Cable Diameter N/A
Coupling Type N/A
Diagnostics / LEDs No
Diagnostics Port No
Gender N/A
Keyway None
Material - Connector Body Polypropylene
Material - Coupling Nut N/A
Material - Plating Mating Silver
Net Weight 7.257/g
Orientation Straight
Pitch - Mating Interface 11.00mm
Poles 2
Temperature Range - Operating -40°C to +90°C
Wire Size AWG N/A

Electrical
Current - Maximum per Contact 16.0A
Voltage - Maximum 250V AC / 300V DC

Material Info
Engineering Number B222000N2

Reference - Drawing Numbers
Packaging Specification PK-121013-B22-001
Sales Drawing SD-121012-047



Series image - Reference only

EU ELV
Not Relevant

EU RoHS **China RoHS**
Not Reviewed
REACH SVHC
Not Contained Per -
ED/30/2017 (7 July
2017)
Halogen-Free
Status
Low-Halogen
For more information, please visit [Contact US](#)

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[121012](#) Series