




## TXR41AB00-1206AI2 Product Details

[!\[\]\(003082e50e3009141f59bd5df831749f\_img.jpg\) Share](#) [!\[\]\(f439ede8735757e3190eab35e168f1de\_img.jpg\) Print](#) [!\[\]\(f5c165e0bd35116675db6686a30b1fea\_img.jpg\) Email](#)

TXR41AB00-1206AI2

### Braid, Fixed, Spin and Tinel Lock Adapters

[Not EU RoHS or ELV Compliant](#)

#### Product Highlights:

- Applies To Cable
- Style = Tinel Lock Braided
- Connector Code = 41
- Straight
- Shell Size = 12, 13

[View all Features](#)

TE Internal Number: 890175-000

[!\[\]\(56549452e01ca28bdf2500ced9653143\_img.jpg\) Add to My Part List](#)[!\[\]\(1f56542a42e2413e44a2b2023033aa2e\_img.jpg\) Request Sample](#)[!\[\]\(19d44b37fb4fa155bf9d60c77a3d3cb2\_img.jpg\) Find Similar Products](#)[!\[\]\(5a351309c3b87e4420622c1f0e57efc0\_img.jpg\) Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [Tinel-Lock Adapter](#) (PDF, English)

#### Related Products:

- [Tooling](#)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- [Style](#) = Tinel Lock Braided
- [Angle](#) = Straight
- [Shell Size](#) = 12, 13
- Finish = Cadmium Plating over Electroless Nickel
- Material = Aluminum Alloy
- Color = Olive Drab

#### Configuration Features:

- [Braid](#) = Preattached Single 36 AWG Braid
- Material Code = A

#### Industry Standards:

- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process

#### Conditions for Usage:

- Applies To = Cable

#### Other:

- Brand = Raychem

#### Electrical Characteristics:

- [Boot Diameter \(mm \[in\]\)](#) = 17.14 [0.675]
- [Entry Diameter \(mm \[in\]\)](#) = 9.50 [0.380]
- Finish Code = B

#### Body Features:

- [Connector Code](#) = 41
- [Entry Size](#) = 6
- [Cable Diameter \(Max.\) \(mm \[in\]\)](#) = 9.02 [0.355]

### Corporate Information

[Who We Are](#)[Investors](#)[News Room](#)[Supplier Portal](#)[Careers](#)

### Quick Links

[Check Distributor Inventory](#)[Cross Reference](#)[Find Documents & Drawings](#)[Product Compliance Support Center](#)[Site Map](#)

### Customer Support

[Email or Chat With Us](#)[Find a Phone Number](#)[Search Knowledge Base](#)[Manage your Account](#)

### Keep Me Informed

Receive TE News, Events &amp; Technology Updates

Enter your email address 