



REV.	DATE	ECR NO.	DESCRIPTION
NC	03/19/10	XXXXXX	INITIAL RELEASE



RECOMMENDED
MOUNTING HOLE

1. FREQUENCY RANGE: DC 0-3 GHz
2. VSWR(RETURN LOSS): 1.15, MAX.

				UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.		APPROVALS		DATE	Amphenol Connex
6	COVER	BRASS	GOLD	1	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 - .315 = ± 0.007" .315 - 1.180 = ± 0.015" 1.180 - 4.724 = ± 0.020"	DRAWN	M.ZHANG	03/19/10	
5	CONTACT PIN	BRASS	GOLD	1		CHECKED			
4	INSULATOR	PTFE	NATURAL	1		ISSUED			
3	INSULATOR	PTFE	NATURAL	1		SHEET	1 OF 1		
2	CONTACT PIN	BER. COPPER	GOLD	1	DO NOT SCALE DRAWING	CAD FILE C:/CONNEX/282100-75.DWG			PART DESCRIPTION
1	BODY	BRASS	GOLD	1					1.0/2.3 R/A BULKHEAD PCB RECEPT. JACK (75 ohm)
DESCRIPTION				QTY					PART NO.
									282100-75
									DWG. NO. 282100-75.DWG
									REV. D
									SIZE A
									SCALE NA