

SurgeArrest Home/Office

APC Power-Saving Home/Office SurgeArrest, 8 Outlets with Phone Protection, 120V



Professional-grade Protection for Computers and Electronics

Includes: Telephone Cable, User Manual



Output

Number of Outlets	8
Receptacle Style	NEMA 5-15R

Input

Input Frequency	50/60 Hz
Input Connections	NEMA 5-15P 
Cord Length	1.83 meters
Maximum Input Current	15A

Surge Protection and Filtering

Surge energy rating	2030 Joules
EMI/RFI Noise rejection (100 kHz to 10 58 dB MHz)	
Peak Current Common Mode	144 kAmps
NM Surge Response Time (ns)	1 ns
Data Line Protection	RJ-11 Modem/Fax protection (two wire single line)
Let Through Voltage Rating	< 400

Physical

Net Weight	0.55 KG
------------	---------

Maximum Height	267.00 mm
Maximum Width	122.00 mm
Maximum Depth	38.00 mm
Shipping Weight	0.96 KG
Shipping Height	362.00 mm
Shipping Width	248.00 mm
Shipping Depth	44.00 mm
Master Carton Units	6.00
Master Carton Dimensions (Length x Width x Height)	371 x 327 x 414 mm
Master Carton Weight	7.18 KG
SCC Codes	1073130426922 6
Color	White
Units per Pallet	216.00

Environmental

Operating Environment	0 - 45 °C
Operating Relative Humidity	0 - 95%
Operating Elevation	0-3000 meters
Storage Temperature	-5 - 45 °C
Storage Relative Humidity	0 - 95%
Storage Elevation	0-15000 meters

Conformance

Regulatory Approvals	ETL,UL 1449
Standard Warranty	Lifetime
UL 1449 TVSS Rating	<400V
Environmental Compliance	RoHS