

24-Port 1U Rackmount Cat6 110 Patch Panel, 568B, RJ45 Ethernet

MODEL NUMBER: **N252-024**



Highlights

- 19-in. rackmount ready, 1U height (1.75")
- EIA/TIA 2/32 spacing
- 110 type punchdown termination
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

- Cat6 Patch Panel 568B- 24 Port, 1U

Description

Tripp Lite's Category 6 Patch Panels offer you all the functionality and compatibility as any name brand. Each panel comes with 110-type termination, while meeting and exceeding EIA/TIA TSB-40 Cat6 connecting hardware specifications. Color coded for both EIA/TIA 568A & 568B installations. 24 ports ensure a wide range of plug-n-play options. The clear numbering on both the front and back of each panel gives you a quick and easy way to identify cable runs and the high density 19in panel design will save you valuable space in on the rack.

Features

- Cat6
- UL approved
- Ports clearly numbered both on front and back
- Labels on front enable each port to be named
- Color coded label on back offers both EIA/TIA 568A & 568B wiring
- Metal frame
- EIA/TIA 2/32 spacing
- Rack mountable on a 19 rack (1U of space)

Specifications

General Info	
Product Group	PATCH PANELS & KEYSTONE JACKS
TAA Compliant	Yes
OVERVIEW	
Style	Cat6/6e/6a



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Model Type	Patch Panels
Cable Type	Cat6/6a
UPC ASSIGNMENT	
Unit Carton UPC#	037332120038
PHYSICAL	
Color	Black
CONNECTIONS	
Connector A	110-TYPE TERMINAL (X24)
Connector B	RJ45 (FEMALE) (X24)
Ports	24
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.