


THIS DOCUMENT CONTAINS DATA PROPRIETARY TO PROJECTS UNLIMITED, INC. ANY USE OR REPRODUCTION, IN ANY FORM, WITHOUT PRIOR WRITTEN PERMISSION OF PROJECTS UNLIMITED, INC. IS PROHIBITED.
© 2005, Projects Unlimited Inc.

SPECIFICATIONS

PARAMETERS	VALUES	UNITS
RATED VOLTAGE	10	Vp-p
OPERATING VOLTAGE RANGE	1 ~ 30	Vp-p
RATED CURRENT (MAX)	9	mA
CAPACITANCE	11000±30%	pF
MINIMUM SPL @ 10 CM	80	dBA
RESONANT FREQUENCY	5000±500	Hz
OPERATING TEMPERATURE	-30 ~ +85	°C
STORAGE TEMPERATURE	-40 ~ +95	°C
HOUSING MATERIAL	ABS	—
TERMINAL MATERIAL	LEAD WIRE	—
WEIGHT	1.0	grams

REVISIONS

LTR	DESCRIPTION	DATE	APPROVED
—	RELEASED FROM ENGINEERING	8/05/05	



NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS.
2. SPECIFICATION SUBJECT TO CHANGE OR WITHDRAWAL WITHOUT NOTICE.
3. THIS PART IS RoHS 2002/95/EC COMPLIANT.

FILE NAME
AT-1750-TFL-LW95-R.DWG

UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN MILLIMETERS, TOLERANCES ARE ±0.5 AND ANGLES ARE ±3°.		 projects® unlimited Dayton, Ohio									
<table border="1"> <tr> <th>APPROVALS</th> <th>DATE</th> </tr> <tr> <td>DRAWN <i>J.A.F.</i></td> <td>8/05</td> </tr> <tr> <td>CHECKED <i>E.P.</i></td> <td>8/05</td> </tr> <tr> <td>APPROVED <i>B.R.</i></td> <td>8/05</td> </tr> </table>		APPROVALS	DATE	DRAWN <i>J.A.F.</i>	8/05	CHECKED <i>E.P.</i>	8/05	APPROVED <i>B.R.</i>	8/05	TRANSDUCER (PIEZO)	
APPROVALS	DATE										
DRAWN <i>J.A.F.</i>	8/05										
CHECKED <i>E.P.</i>	8/05										
APPROVED <i>B.R.</i>	8/05										
<table border="1"> <tr> <td>SIZE A</td> <td>DRAWING NO. AT-1750-TFL-LW95-R</td> </tr> </table>		SIZE A	DRAWING NO. AT-1750-TFL-LW95-R	<table border="1"> <tr> <td>SCALE: N.T.S.</td> <td>SHEET 1 OF 1</td> </tr> </table>		SCALE: N.T.S.	SHEET 1 OF 1				
SIZE A	DRAWING NO. AT-1750-TFL-LW95-R										
SCALE: N.T.S.	SHEET 1 OF 1										
DO NOT SCALE DRAWING											