


NOTES: UNLESS OTHERWISE SPECIFIED

1. P/N: PICO
HOUSING & PLUNGER: MOLDED NYLON TYPE 6,6.
AVAILABLE IN TEN COLORS.
CONTACT BLADE: BERYLLIUM COPPER, GOLD PLATED
PER MIL-G-45204 B TYPE 1
0.00001" [0.000254] THK MINIMUM.
SPRING: STAINLESS STEEL TYPE 302.

2. P/N: 9205-HS
HEAT SHRINK: MOLDED NYLON. AVAILABLE IN BLACK.
BODY: BRASS, 40UIN [1.02UM] MIN GOLD OVER NICKEL
PLATED.
CONTACT: BeCu OR PHOSPHOR BRONZE, 1.02UM(40UIN) MIN
GOLD OVER NICKEL PLATED.

3. P/N W-701/COLOR
28AWG 19X40 TINNED COPPER
0.047 [1.19] O.D. PVC INSULATION
AVAILABLE IN TEN COLORS.

4. PERFORMANCE
MAXIMUM CURRENT: 1.0 AMPS
MAXIMUM VOLTAGE: 600 W.V.D.C.
MAXIMUM TEMPERATURE: 221°F (105°C)



		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS ANGLES ± .XX ± ± .XXX ±		CONTRACT NO.		DESCRIPTION	
				APPROVALS		PICO HOOK TO 0.025 [0.64] SQUARE SOCKET	
				DRAWN		SIZE [CODE IDENT NO. DRAWING NO.]	
				APPROVED BY		A 08505 P703	
		MATERIAL SEE NOTE.				SCALE 1:1	
		FINISH SEE NOTE.				SHEET 1 OF 1	
		NEXT ASSY USED ON				REV.	
APPLICATION		DO NOT SCALE DRAWING					