




MATERIAL NUMBER	OLD PART NUMBER	FINISHED LENGTH
130010-0210	113020A01F010	1.00" +.75" -0 [1.3M +19.1 -0]
130010-0214	113020A01F030	3.00' +1.75" -0 [1.9M +44.5 -0]
130010-0221	113020A01F060	6.00' +2.19" -0 [1.8M +55.6 -0]
130010-0226	113020A01F090	9.00' +3.50" -0 [2.7M +88.9 -0]
130010-0228	113020A01F120	12.00' +3.50" -0 [3.7M +88.9 -0]
130010-0233	113020A01F150	15.00' +6.50" -0 [4.6M +165.1 -0]
130010-0238	113020A01F200	20.00' +6.50" -0 [6.1M +165.1 -0]
130010-0241	113020A01F250	25.00' +12.50" -0 [7.6M +317.5 -0]



MALE FACE VIEW



FEMALE FACE VIEW

1	GREEN-YELLOW	1
2	BLACK	2
3	WHITE	3

WIRING DIAGRAM

ITEM	COMPONENT	MATERIAL	FINISH
1	INSERT	PVC	YELLOW
2	CONTACT SOCKET	COPPER ALLOY	GOLD OVER NICKEL
3	CONTACT PIN	COPPER ALLOY	GOLD OVER NICKEL
4	COUPLING NUT	ZINC DIE CAST	BLACK E-COATED
5	OVERMOLD	PVC	YELLOW
6	CABLE- 16AWG, (65 X #34 COPPER STRANDING), 3 CONDUCTOR, 600V, ST00W, ST	PVC	YELLOW
7	LABEL	MYLAR	BLACK/YELLOW

VOLTAGE RATING	600 VAC/VDC
AMPERAGE RATING	13 AMPS
PROTECTION	IP67
OPERATING TEMPERATURE	-20°C TO 105°C
UL CERTIFICATIONS	UL RECOGNIZED, FILE NO. E152210
CSA CERTIFICATIONS	CSA CERTIFIED, FILE NO. LR6837

RLSD DRAWING EC NO: WNA2009-0849 DRWN: BWOODMAN 6/10/09 CHKD: ----- APPR: JFMURPHY 2009/07/08	DESCRIPTION	QUALITY SYMBOL	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE IN/MM		SCALE ----	DESIGN UNITS ----	THIRD ANGLE PROJECTION		
		 =0		mm	INCH	DRAWN BY BW	DATE 2009/03/30	TITLE MINI-CHANGE CORDSET 3 POLE MALE/FEMALE 16 AWG PVC CABLE MOLEX INCORPORATED				
		 =0	4 PLACES	±---	±---	CHECKED BY VO	DATE 2009/03/30					
			3 PLACES	±---	±---	APPROVED BY	DATE					
			2 PLACES	±---	±.01	----	----					
			1 PLACE	±0.3	±---	MATERIAL NO. SEE CHART		DOCUMENT NO. SD-130010-002		SHEET NO. 1 OF 1		
			ANGULAR ±---°			SIZE C		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS										

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1300100228