





PRODUCT NUMBER
77336-YXXLF

- LEAD FREE, SEE NOTE 5.
- TOTAL NB OF POSITION 04 TO 64
SEE SHEET 2
- OPTIONAL STRAIN RELIEF
SEE SHEET 2


- NOTES:
- 1 - MATERIAL: BASE AND COVER: 30% GLASS FILLED POLYESTER FLAME RETARDANT PER UL-94-V0
COLOUR GREY
STRAIN RELIEF: UNREINFORCED THERMOPLASTIC FLAME RETARDANT PER UL-94-V0
COLOUR GREY
CONTACT: BERYLLIUM COPPER
 - 2 - PLATING: 0.76µm Au OVER 1.27 µm Ni MIN
IN CONTACT AREA, REMAINDER OF PRODUCT (IDC PART) 1.27µm Ni MIN.
 - 3 - TRIANGLE NOT MOLDED-IN ON 2x2 AND 2x3 POSITIONS WITH CENTRAL KEY
 - 4 - FOR PRINTING SPECIFICATION SEE TA 812.
 - 5 - THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS PER GS-22-008.
PACKAGING SPECIFICATION AS PER GS-14-920.

mat'l. code		surface		tolerance	projection	product family	
SEE NOTES		ISO 1302		ISO 416 ISO 1101		2.54MM IDC	
Ltr	ecn no	dr	date	tolerances unless otherwise specified		title	
X	F08-0270	LMU	06.08.12	angles	XXX ±0.3	QUICKIE III FEM CuBe	
Y	F06-0274	LMU	06.09.25	Linear	XXX ±0.13		
					XXX ±0.05	scale 5:1	
T	F20556	DLE	02.10.11	dr	P NIZZI	94.02.11	dwg no
U	F03019	DLE	03.01.23	engr	JM PHAMVAN	93.03.25	
V	F04-0166	LMU	04.04.08	chr	O MATHEVON	93.03.25	77336
W	F05-0109	JCO	05.01.17	appd	JM P	94.02.10	
sheet	revision	Y	V				CUSTOMER Drawing
index	sheet	1	2				


PRODUCT NUMBER	SIZE	DIM "A"	DIM "B"	DIM "C"	DIM "S"	SLOT STYLE
77336-X04LF	2x 2	9.54	2.54	9.46	5.66	NO SLOT
77336-X06LF	2x 3	12.08	5.08	12.00	8.20	RIGHT IF NO KEY
77336-X08LF	2x 4	14.62	7.62	14.54	10.74	RIGHT IF NO KEY
77336-X10LF	2x 5	17.16	10.16	17.08	13.28	RIGHT SLOT
77336-X14LF	2x 7	22.24	15.24	22.16	18.36	RIGHT SLOT
77336-X16LF	2x 8	24.78	17.78	24.70	20.90	2 SLOTS
77336-X18LF	2x 9	27.32	20.32	27.24	23.44	2 SLOTS
77336-X20LF	2x 10	29.86	22.86	29.78	25.98	2 SLOTS
77336-X24LF	2x 12	34.94	27.94	34.85	31.06	2 SLOTS
77336-X26LF	2x 13	37.48	30.48	37.40	33.60	2 SLOTS
77336-X30LF	2x 15	42.56	35.56	42.48	38.68	2 SLOTS
77336-X34LF	2x 17	47.64	40.64	47.56	43.76	2 SLOTS
77336-X40LF	2x 20	55.26	48.26	55.18	51.38	2 SLOTS
77336-X44LF	2x 22	60.34	53.34	60.26	56.46	2 SLOTS
77336-X50LF	2x 25	67.96	60.96	67.88	64.08	2 SLOTS
77336-X60LF	2x 30	80.66	73.66	80.58	76.78	2 SLOTS
77336-X64LF	2x 32	85.74	78.74	85.66	81.86	2 SLOTS




WITHOUT STRAIN RELIEF



WITH LOW PROFILE STRAIN RELIEF



WITH STANDARD STRAIN RELIEF



WITH LATCHING STRAIN RELIEF

AFTER TERMINATION SIDE VIEW OF ASSEMBLY (* LATCHING DIM ON HEADER)

77336-7YYLF		●				●	724
77336-6YYLF	●					●	624
77336-5YYLF		●			●		504 524 530
77336-4YYLF		●		●			
77336-3YYLF		●	●				304
77336-2YYLF	●				●		204 224 230
77336-1YYLF	●			●			
77336-0YYLF	●		●				004
PRODUCT NUMBER	WITH CENTRAL KEY	WITHOUT CENTRAL KEY	STANDARD	WITHOUT STRAIN RELIEF	LOW PROFILE	LATCHING	DASHES NOT AVAILABLE

mat'L code				surface ISO 1302 ✓ ISO 416 ISO 1101		tolerance ISO 416 ISO 1101		projection 		product family QKIE FEM			
lfr	ecr no	dr	date	tolerances unless otherwise specified				title		EURO QUICKIE 0.76 µm Au			
P	F50100	PNZ	95.02.07	angles				mm [inch]					
R	F10586	DLE	01.10.24	Linear									
S	F20194	DLE	02.04.10					scale N/A					
T	F03019	DLE	03.01.23	dr	P	NIZZI	94.02.10			dwg no		sheet 2 of -	size
U	F06-0270	LMU	06.09.12	engr	JM	PHAMVAN	94.02.10			77336		A2	
V	F06-0274	LMU	06.09.25	chr	O	MATHEVON	91.10.31			type		CUSTOMER Drawing	
				appd	JM	P	94.02.10						
sheet index		revision sheet											