



## SOCKET SETS



S910

## SOCKET SETS 1/4" AND 1/2"

**RS 361-2331**



- 1/4" and 1/2" sockets, and combination spanners set
- High performance alloy steel
- Matt finish
- ISO 1174
- DIN 3120
- Case: High Density Polythene (HDPE)

- 12 pcs 1/4" hex sockets:  
4, 4.5, 5, 5.5, 6, 7, 8, 9, 10, 11, 12, 13 mm
- 10 pcs 1/4" hex deep sockets  
4, 5, 6, 7, 8, 9, 10, 11, 12, 13 mm
- 13 pcs 1/2" hex sockets:  
10, 11, 12, 13, 14, 15, 17, 19, 22, 24, 27, 30, 32 mm
- 2 pcs 1/4" extension bars 50 mm / 2" and 100 mm / 4"
- 1 pc 1/4" sliding T-bar
- 1 pc 1/4" universal joint
- 1 pc 1/4" bit holder
- 1 pc 1/4" bit adapter
- 1 pc 1/4" spinner with 2-component handle
- 1 pc 1/4" magnetic adapter
- 5 pcs 1/4" bits Phillips: PH 0, 1, 2, 3, 4
- 3 pcs 1/4" bits slotted: 4, 5.5, 7 mm
- 3 pcs 1/4" bits Pozidriv: PZ 1, 2, 3
- 6 pcs 1/4" bits Hex: 3, 4, 5, 6, 8, 10 mm
- 8 pcs 1/4" bits TORX®: T 8, 10, 15, 20, 25, 27, 30, 40
- 3 pcs 5/16" bits TORX®: T 45, 50, 55
- 2 pcs 1/2" extension bars 5" & 10"
- 1 pc 1/2" universal joint
- 1 pc 1/2" spark plug socket hex 21 mm (13/16")
- 1 pc 1/2" x 5/16" bit holder
- 1 pc 1/2" T-adaptor
- 3 pcs L-keys hex: 1.5, 2, 2.5 mm
- 1 pc 1/4" ratchet, 60 teeth / 6° action angle, quick release
- 1 pc 1/2" ratchet, 60 teeth / 6° action angle, quick release
- 4 pcs flex head wrenches: 8-9, 10-11, 12-13, 14-15 mm
- 6 pcs combination spanners: 8, 10, 12, 13, 14, 17 mm on a practical removable tool-rack
- 1 pc removable three section plastic box with lid