

Example: T25E-C16


T	25	F	C	16
PANDUIT Spiral Wrap Cut Tubing	Outside Diameter 12 = 1/8" (3.17mm) 25 = 1/4" (6.35mm) 38 = 3/8" (9.52mm) 50 = 1/2" (12.70mm) 62 = 5/8" (15.87mm) 75 = 3/4" (19.05mm) 100 = 1" (25.40mm)	F = POLYETHYLENE & WEATHER RESISTANT POLYETHYLENE R = V2 FLAME RETARDANT FR = V0 FLAME RETARDANT N = NYLON T = TEFLON NZFR = V0 FLAME RETARDANT HALOGEN FREE NYLON	X = 10 feet Q = 25 feet L = 50 feet C = 100 feet T = 200 feet TL = 250 feet D = 500 feet M = 1000 feet	Color Suffix See Table Below

COLOR AVAILABILITY

COLOR	COLOR SUFFIX	MATERIAL							
		POLYETHYLENE	WEATHER RESISTANT POLYETHYLENE	FLAME RETARDANT POLYETHYLENE V2 RATING	FLAME RETARDANT POLYETHYLENE V0 RATING	FLAME RETARDANT HALOGEN FREE NYLON V0 RATING	NYLON	WEATHER RESISTANT NYLON	TEFLON
NATURAL (CLEAR)	LEAVE BLANK	X		NATURAL COLOR IS WHITE	NATURAL COLOR IS WHITE		X		X
WEATHER RESISTANT BLACK	0		X					X	
BLACK	20			X	X	X			
BROWN	1	X							
RED	2								
ORANGE	3	X							
YELLOW	4	X							
GREEN	5	X							
BLUE	6	X							
PURPLE	7	X							
GRAY	8	X							
WHITE	10	X							
PINK	16	X							

Notes:

- Refer to Panduit Catalogs for any additional information.
- For roll sizes larger than 10 ft., splicing may occur. For additional information, contact Tech.Support at 1-800-777-3300.
- Refer to Panduit Catalogs for dimensional data.
- Colors are stocked for 1/4" and 1/2" Polyethylene. Other sizes available, consult factory.



CAD FILENAME/LAYERS

G00239HA_DC_SPIRALWRP_01

PANDUIT

CORP.

TINLEY PARK, ILLINOIS

SPIRAL WRAP
(CUSTOMER DRAWING)UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
 (.X) (.XXX)
 (.XX) ANGLES ---

 UNLESS OTHERWISE SPECIFIED,
 ALL DIMENSIONS ARE GIVEN
 IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY JAD

MAT'L:

SCALE NONE

DATE 12-4-00

SEE TABLE

DRAWING NO.

G00239HA

DWG
SIZE
A

I	5-23-13	LEF	VJS	A.ADDED NZFR TO MATRIX B.UPDATED NOTE #2 C.ADDED "CUSTOMER DRAWING" TO TITLE BLK D.REPLACED TOLERANCES IN THE TITLE BLK WITH --	GB0239HA	I	RAMI		
R	12-4-00	JAD		INITIAL RELEASE	GB0239HA	R			
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	