

**Part Number: 74526-4100**

0.50mm Pitch LaneLink™ 10Gbase-CX4 Cable Assembly, 26 AWG, Lanyard Latch, 10.0m Length



Series image - Reference only

Status:	OBSOLETE
Replacement:	Contact Molex
Series:	74526
Category:	Cable Assemblies
Overview:	LaneLink™

Mates With Part(s):

[91525](#) 4X/12X Latch LaneLink™ Receptacle
[91804](#) LaneLink™ Connector

Use With:

[74735](#) X2 Transceiver
[74739](#) XPAK Transceiver

Product Environmental Compliance

EU RoHS: ELV and RoHS Compliant

China RoHS:

REACH SVHC: Not Reviewed

Low-Halogen Status: Not Reviewed

Part Detail**General**

Status	Obsolete
Category	Cable Assemblies
Series	74526
Connector to Connector	4X Plug-to-4X Plug
Overview	LaneLink™
Product Name	10Gbase-CX4, 4X, LaneLink™

Physical

Cable Length	10.0m
Circuits (Loaded)	16
Gender	Plug/Plug
Lock to Mating Part	Yes
Packaging Type	Bag
Single Ended	No
Waterproof / Dustproof	No
Wire Insulation Diameter	N/A
Wire Size AWG	26
Wire/Cable Type	Round

Electrical**(Please review the Product Specification for specific details.)**

Current - Maximum per Contact	0.5A
Impedance	100Ω
Shield Type	Full Shield
Shielded	Yes
Voltage - Maximum	30V AC

Material Info

UPC	800756825106
-----	--------------

Reference - Drawing Numbers

Sales Drawing	SD-74526-400
---------------	--------------

Application Tooling

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling

[Check our list of old tooling that used to be available for this part](#)