

Specifications:

Sound level Category	Low Sound Level
Mode of Operation	Continuous - Low Frequency
Mounting	Panel (see note B)
Voltage Rating	6 to 28 Vdc
Frequency	1900 Hz ± 300 Hz
Loudness (Min. Voltage)	55 to 65 dB(A) min. @ 2 FT and 6 Vdc
Loudness (Max Voltage)	65 to 75 dB(A) min. @ 2FT and 28 Vdc
Current Draw	3 mA Max @ 6 Vdc
Current Draw	11 mA Max @ 28 Vdc
Storage Temperature	-40°C to +85°C
Operating Temperature	-30°C to +65°C
Weight (Typical)	1.6 oz (45 g)
Housing	6/6 Nylon and Color Black
Options	For other options contact factory

Dimensions: Inches (mm)
RoHS Compliant
