


RACK & PANEL CONTACTS



✓ Active

TE CONNECTIVITY (TE)

PIN CONTACT, SZ 16, NIC 600

AMP | NC

208268-2

TE Internal Number: 208268-2

EU RoHS Compliant with Exemptions

EU ELV Compliant with Exemptions

Contact Type Pin

Contact Size 16

Length 25.5 mm [1.004 in]

Contact Mating Area Plating Material Gold

Connector & Contact Terminates To Wire & Cable

 **PRODUCT DRAWING**
English

 **3D PDF**

DOCUMENTATION

Product Drawings

PIN CONTACT, SIZE 16 ARINC 600 TYPE

PDF [\(TIFF AVAILABLE\)](#)

English

CAD Files

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Customer View Model

2D_DXF.ZIP

English

3D PDF

PDF

English

Instruction Sheets

Instruction Sheet (U.S.)

Application Tooling For Screw-Machine Contacts

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector & Contact Terminates To Wire & Cable

Product Type Contact

Body Features

Body Style Straight

Material Copper Alloy

Color Code None

Contact Features

Contact Angle Straight

Contact Type Pin

Contact Size 16

Contact Mating Area Plating Material Gold

Contact Base Material Leaded Copper

Contact Mating Area Plating Thickness (µm) 1.27 – 2.03

Dimensions

Length 25.5 mm [1.004 in]

Wire Range 20 – 16 AWG [.5 mm²]

Operation/Application

For Use With Mates with Socket

Packaging Features

Packaging Method Package

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF
