


Audio Power Points

174-R130B-EX, 174-R130R-EX

KOBI CONN

Audio Power Points



Dimensions: mm (in.)

SPECIFICATIONS

Current Rating:	10A/250V AC
Insulator Resistance:	500VDC 100MΩ min.
Operating Temperature:	-10°C to +80°C
Dielectric Strength:	1000VAC 1 minute
RoHS Compliant by Exemption	

MATERIALS

Insulation:	Nylon
Metal:	Nickel plated brass

Date Last Revised: 3-6-07

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

KC-301103

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[174-R130R-EX](#) [174-R130B-EX](#)