

MICRO SWITCH

A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY
FREDERICK, MINNESOTA

FED. MFR. CODE 91929

ASSEMBLY — TOGGLE SWITCH

CATALOG LISTING

13AT96-T

13AT96-T

M

DRAWING
NUMBER

ISSUE

35

35

35

35

35

35

35

35

35

35

35

35

35

35

35

35

35

35

35

35

35

35

35

35

35

35

35

35

35

35

REPLACES

RELEASE NO. SR10227

4 MAY 62

4 MAY 62

4 MAY 62

4 MAY 62

4 MAY 62

4 MAY 62

4 MAY 62

4 MAY 62

4 MAY 62

4 MAY 62

4 MAY 62

4 MAY 62

4 MAY 62

4 MAY 62

4 MAY 62

4 MAY 62

4 MAY 62

4 MAY 62

4 MAY 62

4 MAY 62

4 MAY 62

4 MAY 62

4 MAY 62

4 MAY 62

4 MAY 62

4 MAY 62

4 MAY 62

4 MAY 62


4 MAY 62

4 MAY 62

4 MAY 62

4 MAY 62

4 MAY 62



NOTE

1- UNIT INCLUDES CAT. LIST, 22 SM267-T TYPE BASIC SWITCH (2)

2- TERMINALS ARE PLATED FOR SOLDERING

3- NUMERICAL TERMINAL DESIGNATION INK STAMPED ADJACENT STANDARD DESIGNATION

4- BASIC SWITCH HAS 24 K GOLD OVERLAY CONTACT DETERMINED BY BUSHING PIVOT HOLE CENTER

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

ELECTRICAL DATA

SCALE FULL

CONTACT ARRANGEMENT
S P D T (2)

BREAK DISTANCE
.010 MIN

DO NOT SCALE PRINT

30 VOLTS DC RATING

INDUCTIVE	SEA LEVEL	1/2 AMP
	50,000 FT	1/2 AMP
RESISTIVE	SEA LEVEL	1 AMP
	50,000 FT	1 AMP
MAXIMUM INRUSH		2 AMP

UNLESS OTHERWISE SPECIFIED

DIMENSIONS ARE IN INCHES

TOLERANCES ARE:

ONE PLACE	(.0)	$\pm .030$
TWO PLACE	(.00)	$\pm .018$
THREE PLACE	(.000)	$\pm .008$
ANGLES		$\pm$

WEIGHT .06 LB

DRAWN

L S D 17 APR 62

FO-80378

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[13AT96-T](#)