


FLKM HDSUB-78/F

Order No.: 5600455

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=5600455>

VARIOFACE module, with screw connection and high density D-Subminiature female connector, for mounting on NS 32 or NS 35/7,5, no. of pos.: 78, width: 169 mm

Commercial data

GTIN (EAN)	4017918957865
Note	Made-to-order
sales group	I011
Pack	1 pcs.
Customs tariff	85369010
Weight/Piece	0.4391 KG
Catalog page information	Page 253 (IF-2007)

<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

General data

Nominal voltage U_N	125 V
Max. current carrying capacity per branch	1 A
Number of positions	78
Width	169 mm
Height	72 mm
Depth	77 mm
Ambient temperature (operation)	-20 °C ... 50 °C


Ambient temperature (storage/transport)	-20 °C ... 70 °C
Mounting position	Any

Connection data


Connection 1	PCB connection
Connection in acc. with standard	IEC / EN
Type of connection	Screw connection
Number of positions	78
Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12
Stripping length	8 mm
Screw thread	M3
Connection 2	D-SUB connection
Type of connection	Pluggable

Diagrams/Drawings

Product drawing



Circuit diagram



Address

PHOENIX CONTACT Inc., USA
586 Fulling Mill Road
Middletown, PA 17057, USA
Phone (800) 888-7388
Fax (717) 944-1625
<http://www.phoenixcon.com>



© 2010 Phoenix Contact
Technical modifications reserved;