

TS-120-G-A-1

TD-108-G-AA

(2,54 mm) .100"

TS, TD, HTS SERIES

PRECISION MACHINED TERMINAL STRIPS

SPECIFICATIONS

For complete specifications see
www.samtec.com?TS,
www.samtec.com?TD or
www.samtec.com?HTS

Insulator Material:

Black G.F. Polyester (TS, TD)
 Black Liquid Crystal Polymer (HTS)

Terminal Material:

Brass, except Style G is
 Phosphor Bronze

Plating:

Au over 50µ" (1,27 µm) Ni or
 Sn over 100µ" (2,54 µm) Cu
 or 50µ" (1,27 µm) Ni

Operating Temp Range:

-55°C to +125°C with Gold
 -55°C to +105°C with Tin

RoHS Compliant:

Yes

Lead-Free Solderable:

Wave only

RECOGNITIONS

For complete scope
 of recognitions see
www.samtec.com/quality




Mates with:
 SS, SD, HSS, SL,
 SDL, ESS, ESD


Note: Some lengths,
 styles and options are
 non-standard, non-returnable.

TYPE STRIP
1
NO. PINS PER ROW
PLATING OPTION
LEAD STYLE


TS
 = Single
 Row Terminal
 Strip



HTS
 = Single Row
 High Temp
 Terminal Strip



TD
 = Double Row
 Terminal Strip




-G
 = 20µ" (0,51 µm) Gold
 Except -J & -L are
 10µ" (0,25 µm) Gold


-T
 = Tin

01 thru 32
 = TS Series

01 thru 36
 = HTS & TD Series


-AA


Component No. = T-1R5-

-A, -A-1, -A-2



-A Component No. = T-1R0-
 -A-X Component No. = T-1R7

LEAD STYLE	X (DIA)	Y (±.015)
-A	(0,46) .018	(3,96) .156
-A-1	(0,64) .025	(5,33) .210
-A-2	(0,89) .035	(5,33) .210


-C, -C-1, -C-2


-C Component No. = T-1R2-
 -C-X Component No. = T-1R9-


LEAD STYLE	X (DIA)	Y (±.015)
-C	(0,46) .018	(3,96) .156
-C-1	(0,64) .025	(5,33) .210
-C-2	(0,89) .035	(5,33) .210

-G-1


Component No. = T-1R5-

-J


Component No. = S-1P1-

-L-1, -L-2, -L-3


Component No. = S-1W1

LEAD STYLE	Y (DIA)	Z (±.015)
-L-1	(12,95) .510	(17,86) .703
-L-2	(9,14) .360	(14,05) .553
-L-3	(6,60) .260	(11,51) .453

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: +1-800-SAMTEC-9 or +1-812-944-6733 SAMTEC NORTHERN CALIFORNIA • Tel: +1-408-395-5900 SAMTEC SOUTHERN CALIFORNIA • Tel: +1-800-726-8329
 SAMTEC SOUTH AMERICA • Tel: +55 31 3786 3227 SAMTEC UNITED KINGDOM • Tel: +44 01236 739292 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0
 SAMTEC FRANCE • Tel: +33 1 60 95 06 60 SAMTEC ITALY • Tel: +39 039 6890337 SAMTEC NORDIC/BALTIC • Tel: +46 8 4477280 SAMTEC BENELUX • Tel: +44 01236 739292
 SAMTEC ISRAEL • Tel: +972 3 7526600 SAMTEC INDIA • Tel: +91 80 3272 1612 SAMTEC ANZ • Tel: +613 9580 0683 SAMTEC SINGAPORE • Tel: +65 6745 5955 SAMTEC JAPAN • Tel: +81 45 475 1385
 SAMTEC SHANGHAI • Tel: +86 21 6083 3766 SAMTEC SHENZHEN • Tel: +86 755 83776780 SAMTEC TAIWAN • Tel: +886 2 2735 6109 SAMTEC HONG KONG • Tel: +852 26904658 SAMTEC KOREA • Tel: +82 31 717 5685