







SIZE	Part Number	Jack Screw Thread	Packing
25	8655MH2501LF	UNC 4-40	bulk : Qty 60
	8655MH2511LF		individual set 50 sets/carton
	8655MH2502LF	M3	bulk : Qty 60
	8655MH2512LF		individual set 50 sets/carton

NOTE:RoHS INFORMATIONS

-The LF product meets European union Directives and other country regulations as described in GS-22-009

-The product is not intended to be exposed to a manufaturing solder process

-Packaging spec:see GS-14-920



NOTES : for every sizes

Material and finish : Zinc die-cast
nickel plated


Cable strain relief : Zinc die-cast

Jackscrew : Brass, nickel plated
UNC 4-40 or M3 (see tables)

Temperature range : -55°C to +125 °C

Attenuation factor : >40 dB between 10 MHz

Other size details : see on next pages.

spec ref		dr		A Parrenin	2009/05/20			size	A3	scale	3:2			
tolerance std ISO 406 ISO 1101	TOLERANCES UNLESS OTHERWISE SPECIFIED		eng		J Dalibard			2015/09/10	ecn no ELX-B-20414-1					
			chr		J Dalibard			2015/09/10	rel level Released					
			appr		Aymeric Soudy			2015/09/11	product family -					
surface  ISO 1302	linear	0.X		±/			title	STRAIGHT METAL HOODS WITH 2 METAL CLAMPS			dwg no	C-8655-1685C		rev D
		0.XX		±/										
		0.XXX		±/										
	angular	0°		±/°										

1

2

3

4




A

B



C

D

SIZE	Part Number	Jack Screw Thread	Packing
09	8655MH0901LF	UNC 4-40	bulk : Qty 80
	8655MH0911LF		individual set 50 sets/carton
	8655MH0902LF	M3	bulk : Qty 80
	8655MH0912LF		individual set 50 sets/carton



SIZE	Part Number	Jack Screw Thread	Packing
15	8655MH1501LF	UNC 4-40	bulk : Qty 80
	8655MH1511LF		individual set 50 sets/carton
	8655MH1502LF	M3	bulk : Qty 80
	8655MH1512LF		individual set 50 sets/carton



A

B

C

D

spec ref		dr		A Parrenin	2009/05/20	projection	mm	size	A3	scale	3:2	
tolerance std		eng		J Dalibard	2015/09/10			ecn no	ELX-B-20414-1			
ISO 406 ISO 1101		chr		J Dalibard	2015/09/10							
		appr		Aymeric Soudy	2015/09/11	product family		-	rel level		Released	
surface		linear	0.X	±/	FCi	title	STRAIGHT METAL HOODS WITH 2 METAL CLAMPS	dwg no	C-8655-1685C		rev	D
ISO 1302			0.XX	±/								
			0.XXX	±/								
		angular	0°	±/°	www.fci.com	cat. no.	-	Product - Customer Drw		sheet 2 of 4		

2

3

PDS: Rev :D



STATUS:Released

Printed: Sep 11, 2015





Copyright FCI.


SIZE	Part Number	Jack Screw Thread	Packing
37	8655MH3701LF	UNC 4-40	bulk : Qty 40
	8655MH3711LF		individual set 50 sets/carton
	8655MH3702LF	M3	bulk : Qty 40
	8655MH3712LF		individual set 50 sets/carton



PRODUCT WITH
M3 THREAD
JACKSCREWS


SIZE	Part Number	Jack Screw Thread	Packing
50	8655MH5001LF	UNC 4-40	bulk : Qty 40
	8655MH5011LF		individual set 50 sets/carton
	8655MH5002LF	M3	bulk : Qty 40
	8655MH5012LF		individual set 50 sets/carton



spec ref				dr	A Parrenin	2009/05/20	projection 	mm 	size	A3	scale	3:2		
tolerance std ISO 406 ISO 1101	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	J Dalibard	2015/09/10			ecn no	ELX-B-20414-1				
				chr	J Dalibard	2015/09/10			rel level	Released				
				appr	Aymeric Soudy	2015/09/11						product family		-
surface -  ISO 1302	linear	0.X	±/		title	STRAIGHT METAL HOODS WITH 2 METAL CLAMPS			dwg no	C-8655-1685C			rev	D
		0.XX	±/											
		0.XXX	±/											
	angular	0°	±/°	www.fci.com	cat. no.	-	Product - Customer Drw				sheet 3 of 4			


CABLING INSTRUCTIONS

1- Strip the cable and solder or crimp the wires




SCALE 3:2

2-Put the connector into a half hood and tighten the jacket with a metal clamp




SCALE 3:2

3-To get the electrical continuity between the cable outer conductor and the hood tighten the outer conductor with the other metal clamp as shown



SCALE 3:2

4-Mount the jackscrews, the other half hood and tighten with 2 screws



Copyright FCI.

spec ref			dr		A Parrenin	2009/05/20		projection		mm		size		A3	scale		1:1		
tolerance std			eng		J Dalibard	2015/09/10						ecn no		ELX-B-20414-1					
ISO 406 ISO 1101			chr		J Dalibard	2015/09/10						rel level		Released					
TOLERANCES UNLESS OTHERWISE SPECIFIED			appr		Aymeric Soudy		2015/09/11		product family										
					title		STRAIGHT METAL HOODS WITH 2 METAL CLAMPS				dwg no		C-8655-1685C				rev		D
surface			linear		0.X		±/												
ISO 1302					0.XX		±/												
					0.XXX		±/												
			angular		0°		±/°		www.fci.com		cat. no.		Product - Customer Drw				sheet 4 of 4		