


Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du proprietaire. Propriete de c FCI. Droits de reproduction FCI.

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

FCI P/N (NOTE 1)	"L" (NOTE 1)
59899-YXXX	XXX

COMPONENTS		
ITEM	QTY.	DESCRIPTION
1	2	LC DUPLEX S/M CONNECTOR, SUNCALL
2	"L"	CABLE, 2.0MM ZIP, 8.3/125
3	A/R	IDENTIFICATION LABEL



SPECIFICATIONS	
INSERTION LOSS	0.25dB MAX
RETURN LOSS	55dB MIN
FIBER PROTRUSION	50nm MAX
APEX OFFSET	45um MAX
FIBER UNDERCUT	SEE TELECORDIA GR-326

- NOTES:
1. FCI P/N CONSISTS OF DWG NO, A DASH, AND A SUFFIX YXXX WHERE Y IS THE UNIT OF LENGTH (Y=M IS METERS AND Y=F IS FEET) AND WHERE XXX IS THE LENGTH "L". (EX. 59899-F004 IS 4 FT IN LENGTH.)

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		Electronics	
ltr	ecn no	dr	date	linear	NOMINALS ONLY	projection	mm	title	www.fciconnect.com
A	V11463	JKK	4/17/01		UNLESS NOTED				
B	V12374	JRW	12/3/01	angles				CA, F, LC-LC, 2.0mm ZIP, SM-8.3	
				dr	J. KILE	4/17/01		product family FIBER OPTICS	code
				enrg	S.K. CLARK	4/17/01		size	213
				chr	S.K. CLARK	4/17/01		dwg no	sheet
				appd	S.K. CLARK	4/17/01		A4 59899	1 of 1
sheet index	revision sheet	B	1						

cage code
22526

ACAD

PDM: Rev:B

STATUS Released

Printed: Apr 08, 2008