

P624 Product Details

 Share

 Print

 Email

No Image Available

P624

NEMA Terminal Blocks

Not reviewed for RoHS Compliance

Product Highlights:

- 600 Series Block Series
- NEMA Product Line
- Block Type = Flat Base
- Contact Configuration = Tubular Screw
- Medium Duty Application

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

TE Internal Number: 6-1437393-9

 Superseded

[Search for Replacement Parts](#)

 [Add to My Part List](#)



[Request Sample](#)



[Find Similar Products](#)



[Buy Product](#)

Documentation & Additional Information	
Product Drawings: - None Available Catalog Pages/Data Sheets: - None Available Product Specifications: - None Available Application Specifications: - None Available Instruction Sheets: - None Available CAD Files: - None Available	Additional Information: Product Line Information Additional Product Images: Line Drawing Related Products: Tooling

Product Features (Please use the Product Drawing for all design activity)	
Product Type Features: - Product Line = NEMA - Screw Size = 10-32 Slotted Pan Head Electrical Characteristics: - Voltage Rating (VAC) = 300 - Amperes (A) = 50.0 Body Features: Block Series = 600 Series Block Type = Flat Base - Mount Style = Direct Mount (Flat Base) Wire Range (Solid and Stranded)[MCM] (AWG) = 18-8 Blown Fuse Indicator = Without Blown Fuse Indicator Type = None - Wire Strip Length (mm [in]) = 8.74 [0.344] Contact Features: - Contact Configuration = Tubular Screw - Pitch (mm [in]) = 9.53 [0.375] Housing Features: Housing Material = Polypropylene Industry Standards: RoHS/ELV Compliance = Not reviewed for ELV/RoHS compliance Lead Free Solder Processes = Not reviewed for lead free solder process Operation/Application: - Application = Medium Duty Packaging Features: - Terminals Per Foot = 30 Other: - Brand = Buchanan	