



Search Results

- Evaluate
- [FAQ's](#)
- How to Buy
- [Bill of Material](#)
 - [Favorite Products List](#)
 - [Locate Distributor](#)

[Home](#) > [Products Overview](#) > [Search Results](#) >

Current refinements (click to remove) [Search Tips](#)

Text Search: 'HSTTV19-Q'

Your search criteria matched only one product, shown below

HSTTV19-Q



Flexible Polyolefin VW-1 DRY-SHRINK™ Heat Shrink Tubing on 25 ft. (7.5M) Reels

- For dry locations
- Highly flame retardant
- Fast Shrink Time
- Material Type: Highly Flexible Crosslinked Polyolefin
- Shrink Ratio: 2:1
- Temperature Range: -67°F to 257°F (-55°C to 125°C)
- Voltage: 600V
- UL VW-1 Recognized, CSA Certified
- Mil Spec: AMSDTL-23053/5 Class 3

Part Number	HSTTV19-Q
RoHS Compliancy Status	Compliant
Part Description	Thin Wall Polyolefin Heat Shrink (UL224 VW1)
Material	Polyolefin cross-linked
Color	Black
CSA Certified	Yes
Military Specification	AMS-DTL-23053/5 Class 3
UL Recognized	E122770
CE Compliant	No
CE Marking	No
Flammability Rating	UL224 VW-1
Length Per Reel (ft.)	25
Length Per Reel (m)	7.6
Max. Recovered I.D. (In.)	.093
Max. Recovered I.D. (mm)	2.4
Min. Expanded I.D. (In.)	.187
Min. Expanded I.D. (mm)	4.8
Nominal Diameter (In.)	.187
Nominal Diameter (mm)	4.8
Nominal Recovered Wall Thickness (In.)	.020
Nominal Recovered Wall Thickness (mm)	0.5
Pricing Description	Heat Shrink Thin VW1, .19"(4.8mm) Dia, Black
Shrink Ratio	2:1
Temperature Range	-67°F to 257°F (-55°C to 125°C)
Min. Order UOM	RL
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.