

# MODEL TLH-5955



International size reference: 2/3AA, ER14335

## TECHNICAL DATA

(Typical values @+ 25°C for batteries stored for one year or less)



|                                          |                   |
|------------------------------------------|-------------------|
| ■ Nominal capacity @ 1.3 mA, to 2 V      | 1.40 Ah           |
| ■ Rated voltage                          | 3.6 V             |
| ■ Maximum recommended continuous current | 75 mA             |
| ■ Maximum pulse current capability       | 150 mA            |
| ■ Weight                                 | 12.5 g (0.441 oz) |
| ■ Volume                                 | 5.2 cc            |
| ■ Operating temperature range            | -55 °C to +125 °C |
| ■ Li metal content                       | approx. 0.5 g     |
| ■ U.L. Component Recognition, MH 12193   |                   |

***TADIRAN  
LITHIUM  
BATTERIES***



### TERMINATIONS & ORDERING NO.

|                            |               |
|----------------------------|---------------|
| SUFFIX- /S STANDARD        | 15-5955-21505 |
| SUFFIX- /T SOLDER TABS     | 15-5955-31505 |
| SUFFIX- /P AXIAL PINS      | 15-5955-41505 |
| SUFFIX- /PT2 RADIAL PINS   | 15-5955-36505 |
| SUFFIX- /TP POLARIZED TABS | 15-5955-52505 |
| SUFFIX- /PT POLARIZED TABS | 15-5955-53505 |



***Extended Temperature Range***

Note: Any presentations in this data sheet concerning performance are for information purpose only and are not construed as warranties either expressed or implied, of future performance.

ECN 1501187 Rev. A 01/06