





THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	2003
© COPYRIGHT 2003	ALL RIGHTS RESERVED.	

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DRN	APPD
		A18	ECR-16-003426		07Apr2016	SL	RR
		A19	ECR-16-003755		24MAY2016	KD	RR
		A20	ECR-16-016334		18NOV2016	FV	RR
		A21	ECR-17-009651		19 JUL2017	RS	DC




3D VIEW FOR REF. ONLY
3 POS. PN 0-284931-3 AS SHOWN
SCALE 5:1



- | | |
|----|--|
| 1 | WIRE RANGE : STRANDED 0.22-0.35 mm ² (INS. DIA. 1.30±0.1) |
| 2 | MATING PART: TAB HEADER P/N 829866;
PCB FRAME P/N 964575 (PCB THK 1.5±0.14 COPPER CLADDING INCLUDED)
SEE PRODUCT SPEC. 108-18056 FOR FRAME APPLICATION |
| 3 | KEYING RIBS TO BE REMOVED BY TERMINATION MACHINE |
| 4 | CUT OFF DIMENSION DUE TO PRODUCTION PROCESS |
| 5 | CIRCUIT No. IDENTIFICATION |
| 6 | TE TRADEMARK (OPTIONAL POSITION) |
| 7 | TAMPOGRAPHIC COLOUR CODE AREA
(P/Ns IDENTIFICATION BEFORE CRIMPING) |
| 8 | PRELIMINARY PART NOT YET RELEASED FOR PRODUCTION |
| 9 | PBT GF |
| 10 | PBT GF, UL94-V0 & GWEPT 750 NO-FLAME, NATURAL |

P/N 0-284931-5 AS SHOWN								
	BLUE	SELECT I VELY 1,2,3,4,5,6,7,8,9,10,11,13	13	2/3	30.0	34.9	1-284931-3	2311506-3
	BLUE	SELECT I VELY 1,3,5,7,9,11	11	-	25.0	29.9	1-284931-1	2-2311506-1
	BLUE	SELECT I VELY 1,3,5,7,8,10	10	-	22.5	27.4	1-284931-0	1-2311505-0
	GREEN	SELECT I VELY 1,3,4,6,8,9	9	-	20.0	24.9	2-284931-9	3-2311505-9
	BLUE	SELECT I VELY 1,2,4,6,7,9					0-284931-9	2-2311505-9
	GREEN	SELECT I VELY 1,3,4,6,7,8	8	-	17.5	22.4	2-284931-8	1-2311505-8
	BLUE	SELECT I VELY 1,2,3,5,6,8					0-284931-8	2311505-8
	GREEN	SELECT I VELY 1,3,5,6,7	7	-	15.0	19.9	2-284931-7	2-2311505-7
	BLUE	SELECT I VELY 1,3,5,7					0-284931-7	1-2311505-7
	BLUE	SELECT I VELY 1,2,4,6	6	-	12.5	17.4	1-284931-6	2-2311505-6
	RED	SELECT I VELY 1,3,4,6	6	-	12.5	17.4	0-284931-6	1-2311505-6
	GREEN	SELECT I VELY 1,2,3,5	5	-	10.0	14.9	4-284931-5	4-2311505-5
	RED	SELECT I VELY 1,5					3-284931-5	3-2311505-5
	-	SELECT I VELY 1,3,5					2-284931-5	2-2311505-5
	BLUE	SELECT I VELY 1,3,5					0-284931-5	-
OB SOLE T E D	RED	SELECT I VELY 1,3	3	2/3	5.0	9.9	5-284931-3	5-2311505-3
	BROWN	SELECT I VELY 1,3		-			4-284931-3	4-2311505-3
	GREEN	SELECT I VELY 1,3					3-284931-3	3-2311505-3
	-	SELECT I VELY 1,3					2-284931-3	2-2311505-3
	BLUE	SELECT I VELY 1,3					0-284931-3	1-2311505-3
	COLOUR CODE 	CONTACT LOADING	HSG POS.	KEYING	DIM.A	DIM.B	 TE P/N	 REV

-	-	-	-	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. FABRIS	27FEB2004	 TE Connectivity						
SEE TABLE	PH. BRONZE, TIN PLATED	IDC RECEPTACLE CONTACT	2	DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD G. TURCO	27FEB2004	NAME DUOPLUG 2.5 FEMALE CONNECTOR STANDARD VERSION (SELECTIVELY LOADED)					
	PBT GLASS FIBER FILLED	FEMALE HOUSING	1				PRODUCT SPEC 108-18056							
Q.TY	MATERIAL	DESCRIPTION	ITEM				APPLICATION SPEC 108-18049-1		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
1	REVISIONE DELL'ASSEMBLATO (REVISION OF EACH ASSY IND)			MATERIAL SEE TABLE		FINISH			A1	00779	C=284931			
0.1% PRE ASSEMBLY (0.1% PRE ASSY)	ELENCO DEI COMPONENTI (PARTS LIST)						WEIGHT		CUSTOMER DRAWING					
									SCALE	2:1	SHEET	1 of 1	REV	A2