



Identification

Part No.

Drawing

Dimensions in mm

Fibre optic cable, double ended,
multi mode, 50 μm

Length: a = 1 m

a = 5 m

a = 10 m

a = 20 m

a = 40 m

a = 50 m

a = 100 m

33 58 211 0010 004

33 58 211 0050 004

33 58 211 0100 004


33 58 211 0200 004

33 58 211 0400 004


33 58 211 0500 004

33 58 211 1000 004

double ended



a = length



Fibre optic cable, single ended,
multi mode, 50 μm

Length: a = 1 m

a = 5 m

a = 10 m

a = 20 m

a = 40 m

a = 50 m

a = 100 m

33 58 111 0010 004

33 58 111 0050 004

33 58 111 0100 004

33 58 111 0200 004


33 58 111 0400 004

33 58 111 0500 004

33 58 111 1000 004

Protection level: IP 65 / IP 67

single ended



a = length

Fibre optic breakout cable ,
multi mode, 50 μm

Length: 10 m

Length: 20 m

Length: 100 m

33 58 751 0100 003

33 58 751 0200 003

33 58 751 1000 003



PUR jacket

2-fibre multi mode 50 μm

Outer diameter: 6.5 mm

Min. bending radius:

Installation: 10.4 cm

Operating: 5.2 cm