







REV.	DATE	ECR NO.	DESCRIPTION
A	10/29/02	—	MODIFY DESCRIPTION
B	02/25/09	100083	UPDATE DRAWING FORMAT



				UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex				
8					DRAWN	GRS	02/25/09						
7					CHECKED								
6	MOUNTING POST	BRASS	BRT. TIN		1					PART DESCRIPTION DUAL PORT BNC PCB MOUNT RECEPTACLE – DIE CAST 75ohm			
5	POST	COPPER	BRT. TIN		1								
4	CONTACT PIN	BER. COPPER	GOLD FLASH		1					PART NO. 112707			
3	CONTACT PIN	BER. COPPER	GOLD FLASH		1								
2	INSULATOR	P.P.	NATURAL		1					DWG. NO. 112707.DWG REV. B SIZE A SCALE NA			
1	BODY	ZINC DIE CAST	NICKEL	1									
	DESCRIPTION	MATERIAL	FINISH	QTY	CAD FILE C:/112/112707.DWG								

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[112707](#)