



Technical drawing of a rectangular box. The overall height is labeled as 0.73 (18.5). The drawing shows a central circular feature with internal details, surrounded by a dashed rectangular frame. The box has a lid and a base, with internal structural lines indicating a complex internal design.



PANDUIT PART NO. *	PANEL DIMENSIONS		WEIGHT LBS. (6) / 100 PCS.
	THICKNESS	HOLE SIZE	
BECP38H25	0.075 (1.9) MAX.	0.25 (6.4)	0.88 (400) @

* 1. SEE CURRENT PRICE SHEET FOR PART
NUMBER SUFFIX DESIGNATION FOR
PACKAGE SIZE AND PART COLOR.



(DIMENSIONS IN PARENTHESES ARE IN METRIC.)

CAD FILENAME/LAYERS G002391B_PB_BECP38H25_01

PANDUIT

CORP. TINLEY PARK, ILLINOIS

BECP38H25
BEVEL ENTRY CLIP

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± N/A (.XXX) ± N/A
(.XX) ± .020 (.5) ANGLES ± 5°

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY LGG

MAT'L 6

SCALE 2X

DATE
02-26-02

6/6 NYLON

DRAWING NO.
GB02391B

DWG
A
SIZE

I	4/21/04	JAD		PANEL THICKNESS WAS .09(2.3) MAX	6802391B	I			
R	2/28/02	LGG		INITIAL RELEASE TRANSFER FROM DRAWING NUMBER G-01801	6802391B	R			
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP		