






LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	OWN / APVD
GP	00	0		RELEASED PER EC OS13-0131-05	23JUN05	BM / JG





⚠ MATERIAL: HOUSING - NYLON MOLDING COMPOUND, 94V-0, GLASS FILLED, BLACK.
TERMINALS - 0.25[.010] THICK BRASS PLATED WITH 0.254 MICRONS[.000010] MINIMUM THICK GOLD OVER 1.016 MICRONS [.000040] MINIMUM THICK PALADIUM NICKEL OVER 0.05 MICRONS[.000002] MINIMUM THICK GOLD IN CONTACT AREAS AND 3.8 MICRONS[.000150] MINIMUM THICK TIN ON SOLDER TINES OVER 2.54 MICRONS[.000100] MINIMUM THICK NICKEL UNDERPLATE.
SHIELD - STAINLESS STEEL, TIN PLATED
STRIKER PLATE- STAINLESS STEEL.

2. PACKAGED IN TAPE AND REEL.


KEY 5-15	5-5558556-5
KEY 4-15	5-5558556-4
KEY 3-15	5-5558556-3
KEY 2-15	5-5558556-2
KEY 1-15	5-5558556-1
KEYING OPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN B. McMASTER 23JUN05	23JUN05	Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
DIMENSIONS: mm [INCHES]		CHK D. GORENC 23JUN05	23JUN05	NAME M. WALMSLEY	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC		APPLICATION SPEC	
0 PLG ± -		1 PLG ± -		2 PLG ± -	
3 PLG ± -		4 PLG ± -		ANGLES ± -	
FINISH		SIZE		CAGE CODE	
MATERIAL		WEIGHT		DRAWING NO	
1		1		A1 00779	
CUSTOMER DRAWING		SCALE		RESTRICTED TO	
		10:1		5558556	
		SHEET		REV	
		1 OF 2		Q	


LDC		DIET		REVISIONS					
GP		00		P	LTR	DESCRIPTION	DATE	OWN	APPO
					—	SEE SHEET 1	—	—	—




SUGGESTED PC BOARD
MOUNTING DIMENSIONS




KEY 4-15
LAN



KEY 3-15
MODEM



KEY 2-15
MULTI-FUNCTION



KEY 1-15
CLOSED



KEY 5-15

KEYING OPTIONS
SCALE 8:1

[illegible]