


IEI Quick Mounting Technology



Compliant with VESA Mounting Standards

IEI panel solutions has four mounting holes compliant with the VESA (Video Electronics Standards Association) mounting standard (75mm x 75mm/100mm x 100mm) on the rear panel for stand mounting and other mounting methods.



1. Stand Mounting

2. V-STAND

3. ARM

4. Wall Mounting

5. In-Wall Mounting

6. Panel Mounting

7. Rack Mounting

8. Din Mounting

1. Stand Mounting


VESA 75/100 Easy Stand



STAND-A/Bxx



Tilt Forward/Backward




STAND-C12 STAND-C19




Tilt Forward/Backward




STAND-A08




STAND-B08



STAND-A19



STAND-A12



Ordering Information

Part Number	Description
STAND-A08	5.6"~8.4" VESA 75x75mm PPC/monitor stand, support up to 5KG, Silver color, RoHS
STAND-B08	5.6"~8.4" VESA 75x75mm PPC/monitor stand, support up to 5KG, Silver color, RoHS
STAND-C12	5.7" ~ 12.1" VESA 100x100mm, 75x75mm PPC/Monitor Stand, support up to 7.5kg, Black color, RoHS
STAND-A12	10"~12.1" VESA 100x100mm PPC/monitor stand, support up to 5KG, Silver color, RoHS
STAND-A19	12.1"~19" VESA 100x100mm PPC/monitor stand, support up to 7.5KG, Silver color, RoHS
STAND-C19	15" ~ 19" VESA 100x100mm, 75x75mm PPC/Monitor Stand, support up to 15kg, Black color, RoHS


VESA 75/100 Universal Stand

Ordering Information

Part No.	Description
STAND-100-RS	- Material: Heavy-duty steel - Adjustable display angle 3kg to 8kg loading capacity - Color: White (Pantone 413C)



STAND-100




Ordering Information

Part No.	Description
STAND-210-R11	- Support VESA 75/100 standard - Weight capacity from 7kg~14kg



STAND-210



1

IEI Mobile Solutions

2

Automation Panel Solutions

3

Video Wall Controller/ Splitter

4


RISC-based Solutions

5


PACsmate Medical Solutions

6




Optional Peripherals

STAND-B19**Ordering Information**

Part No.	Description
STAND-B19-RS	15"~19" VESA 75x75mm/100x100mm PPC/monitor Stand, support from 2.7KG to 7.3KG, Black, RoHS

**VESA 100/200 Lift Stand****STAND-A26**


VESA 100/200 Lift Stand	Model
200x100mm	STAND-A26-R11

**Ordering Information**


Part No.	Description
STAND-A26-R11	19"~26" VESA 75x75mm / 100x100mm / 200x100mm / 200x200mm PPC / monitor Stand, support from 7.3KG to 16.3KG, Black color, RoHS

VESA 100/200/400 Mobile Stand

VESA 100/200/400 Mobile Stand	Model
400x200mm	STAND-M100-R10

STAND-M100**Light POS Stand**

Light POS Stand	Model
	STAND-POS12
	STAND-POS15

**STAND-POS12****STAND-POS15****Ordering Information**

Part No.	Description
STAND-M100	26"~42" VESA 100x100mm/200x100mm/200x200mm/400x200mm/400x400mm PPC/monitor Stand, support up to 100KG, Black, RoHS

Ordering Information

Part No.	Description
STAND-POS12	AFL-12A/B PPC stand, gray color, RoHS
STAND-POS15	AFL-15A/B PPC stand, black color, RoHS

1

IEI Mobile Solutions

2

Automation Panel Solutions

3

Video Wall Controller/ Splitter

4

RISC-based Solutions

5

PACSmate Medical Solutions

6

Optional Peripherals