






INSULATED MOUNTING HOLE
(ACCOMMODATES 1/4" HARDWARE)
(2 PLCS)



- NOTES:
1. UL LISTED AND CSA CERTIFIED. DUAL RATED CU9AL FOR ALUMINUM OR COPPER CONDUCTORS. MEETS OR EXCEEDS ANSI C119.4
 2. WIRE RANGE: 350 kcmil - #10 AWG. ONLY ONE CONDUCTOR PER PORT ALLOWED.
 3. STRIP LENGTH: 1.06 +.06/-0
 4. HEX KEY SIZE: 5/16", TIGHTENING TORQUE 275 IN-LB.
 5. VOLTAGE RATING: 600 V. MAX.
 6. TEMPERATURE RATING: 90° C.
 7. CONNECTOR BLOCK BODY IS MADE FROM ALUMINUM. CLAMPING SCREWS ARE TIN PLATED. PORTS IN CONNECTOR BLOCK ARE PREFILLED WITH AN OXIDE-INHIBITING COMPOUND.
 8. INSULATION MATERIAL IS CLEAR PVC.
 9. CLAMPING SCREW ACCESS PORTS AND ALL CONDUCTOR ENTRY PORTS ARE PROVIDED WITH REMOVABLE PLASTIC CLOSURE PLUGS.
 10. ALL DIMENSIONS SHOWN ARE NOMINAL.
 11. PACKAGE QTY: -2 = 2 PCS
-1 = 1 PCS
 12. THIS PART IS ROHS COMPLIANT.



PART NUMBER	# CONDUCTOR PORTS	DIM "L"	DIM "A"
PCSBMT350-4-2Y	4	6.17	5.00
PCSBMT350-6-2Y	6	8.17	7.00
PCSBMT350-8-2Y	8	10.17	9.00
PCSBMT350-10-1Y	10	12.17	11.00
PCSBMT350-12-1Y	12	14.17	13.00



									C41536_00					
									PANDUIT CORP. TINLEY PARK, ILLINOIS					
									MULTI-TAP INSULATED CONNECTORS WITH MOUNTING HOLES PCSBMT 350 DOUBLE SIDED SERIES					
00	3/06	JHNU	LEM	DRAWING RELEASED - ROHS COMPLIANT		PC00353								
REV	DATE	BY	CHK	DESCRIPTION		ECN #		CUST	PM		DRAWN BY JHNU	CHK'D	SCALE N/A	DRAWING NO. C41536