

SOLID ABS 5638 18 T



Sample photo

Order symbol: ABS 5638 18 T
Product nbr: 5880065
Description: Enclosure, ABS
Remarks: Transparent cover

EAN: 6418074039231
El. number:
Finland: 3423774
Italy: 7410265
Sweden: 2539757
Norway:

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		558	378	180	Ingress Protection (EN 60529): IP 66/67
inch:		22.0	14.9	7.1	Impact Resistance (EN 62262): IK 08
Materials:					Electrical insulation: Totally insulated
Material:		ABS			Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:		RAL 7035			Flammability Rating (UL 746 C 5): UL 94 HB
Cover colour:		Clear transparent			Glow Wire Test (IEC 695-2-1) °C: 650
Cover screws material:		Polyamide			NEMA Class: NEMA 1, 4, 4X, 6, 12, 13
Cover screws colour:		Grey			Certificates:
Gasket material:		Polyurethane			Fimko
Temperatures:					Europe EN 62208: 2003
Short term:		-40 ... 80 °C			Gost R
Continuous:		-40 ... 60 °C			
Short term:		-40 ... 175 °F			
Continuous:		-40 ... 140 °F			
Accessories:					
EKUVT		Mounting plate			
EKUXT		Mounting plate Pertinax			
EKV 32		DIN-35 Mounting rail			
EKUZR		Extension frame			

SOLID 558x378x180

