





REV.	DATE	DESCRIPTION
NC	10/18/06	INITIAL RELEASE
A	10/30/07	REVISE CONTACT PIN TO MALE - BOTH ENDS



RECOMMENDED
MOUNTING HOLE



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex										
8						DRAWN	G.R.S.	10/30/07												
7						CHECKED														
6											PART DESCRIPTION									
5	HEX NUT	BRASS	GOLD	1							SMA REVERSE POLARITY BULKHEAD JACK TO SMA REVERSE POLARITY JACK ADAPTER									
4	LOCK WASHER	BRASS	GOLD	1																
3	CONTACT PIN	BRASS	GOLD	1																
2	INSULATOR	TEFLON	NATURAL	1																
1	BODY	BRASS	GOLD	1						PART NO.										
										132170RP–RP										
DESCRIPTION					MATERIAL		FINISH		QTY		CAD FILE		DWG. NO.		REV.		SIZE		SCALE	
											C:/132/132170RP–RP.DWG		132170RP–RP.DWG		A		A		NA	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[132170RP-RP](#)