


DRAWING NO.
SD214514

CATALOG NO.	WIRE RANGE (AWG/kcmil)	L	W	H	HEX KEY	N
1PLD600-2	#4-600	2.72 [69]	3.00 [76]	2.75 [70]	3/8	2
1PLD600-3	#4-600	4.00 [102]	3.00 [76]	2.75 [70]	3/8	3
1PLD600-4	#4-600	5.28 [134]	3.00 [76]	2.75 [70]	3/8	4
1PLD600-5	#4-600	6.56 [167]	3.00 [76]	2.75 [70]	3/8	5
1PLD600-6	#4-600	7.84 [199]	3.00 [76]	2.75 [70]	3/8	6
1PLD600-8	#4-600	10.40 [264]	3.00 [76]	2.75 [70]	3/8	8
1PLD600-10	#4-600	12.97 [329]	3.00 [76]	2.75 [70]	3/8	10
1PLD600-12	#4-600	15.53 [394]	3.00 [76]	2.75 [70]	3/8	12

FEATURES	BENEFITS
PLASTISOL COVERED AL6061-T6 BODY	SAVES TIME, LOWERS INSTALLATION COSTS, ELIMINATES TAPING.
OXIDE-INHIBITOR IS PRE-INSTALLED	INHIBITS MOISTURE AND CONTAMINANTS FROM ENTERING THE CONTACT AREA
RANGE-TAKING	REDUCES THE NUMBER OF CONNECTORS CARRIED IN INVENTORY

REV.	DATE	DESCRIPTION	ECO	BY	C'K'D.
B	9/22/06	ADDED TEXT NOTE #6	13422	PL	DB



NOTES:

- THIS DRAWING TO BE INTERPRETED PER ANSI Y14.5M.
- CONNECTORS ARE SUPPLIED INDIVIDUALLY LABELED. LABEL INFORMATION INCLUDES CATALOG NUMBER, AND BARCODE.
- END CAPS INSTALLED ON WIRE PORTS AND SET SCREW PORTS.
- ALL CONNECTORS UL LISTED, CSA CERTIFIED FOR AL9CU, 90°C APPLICATIONS, UNLESS OTHERWISE NOTED.
- DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.
- UV RATED INSULATION MATERIAL.

TO ORDER BURNDY® PRODUCTS CALL 1-800-346-4175
MANCHESTER, NH 03109, USA
FOR PRODUCT INFO = <http://www.fciconnect.com>

UV BLACK DISTRIBUTION CONNECTORS

ITEM NO: N/A

CAT NO: 1PLD600- SERIES (TABLE)

SCALE: N/A
DRAWN BY: D RAJUMAR 4/24/02
CHECKER: K HENRY 5/23/02
DSN APPVL: G DITROIA 3/6/02
MFG APPVL: T BONINA 2/27/02
QC APPVL: J BRODEUR 3/5/02
MKT APPVL: A ZWIT 2/27/02
PROD FAM: --
PROJECT #: --
DOCUMENT TYPE: Sales
REL LEVEL: AutoCAD

BURNDY
PRODUCTS

DRAWING NO
SD214514
SHEET 6 OF 13

REV
B