

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300980076](#)
Status: **Active**
Overview: [Strain-Relief Cord Grips](#)
Description: MAX-LOC Strain Relief Cord-Sealing Grip, 1/2" NPT, Straight Male, Cable Diameter 11.10-12.70mm (.437-.500")

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Brochure \(PDF\)](#)

Agency Certification

CSA LR32159
UL E76954

General

Product Family Cable Grips
Series [130098](#)
Eye Type N/A
NEMA Rating NEMA 3R
O-Ring No
Overview [Strain-Relief Cord Grips](#)
Product Name MAX-LOC
Type Strain Relief Grip
UPC 78678872120
Use With 1/2" NPT MAX-LOC Lock Nut [1300990143](#) , MAX-LOC O-Ring, 1/2" NPT [1301800314](#) , 1/2" NPT MAX-LOC Gasket [1300990149](#)

Physical

Approximate Break Strength N/A
Bale Length N/A
Body Style Straight
Cable Diameter 11.10-12.70mm (.437-.500")
Color - Grommet Orange
Gender Male
Material - Body Nylon
Material - Grip N/A
Mesh Length N/A
Net Weight 27.215/g
Number of Holes 1
Thread Size 1/2" NPT

Material Info

Engineering Number 5530

Reference - Drawing Numbers

Sales Drawing 1300980036-000, SD-130098-003



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Relevant

China RoHS

REACH SVHC

Not Relevant

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Relevant

Search Parts in this Series

[130098](#) Series