



Square display LEDs


SEL1020 series




SEL1021 series



SEL1022 series



SEL1024 series



■External dimensions: Unit: mm Tolerance: ± 0.3
 * Resin heap: 1.5 mm Max

Absolute maximum ratings (Ta=25°C)

Symbol	Unit	Ratings
I _F	mA	30
I _{FP}	mA	100
V _R	V	3
Top	°C	−30 to +85
Tstg	°C	−30 to +100

Type No.	Display form (ø: mm)	Type of lens	Emitting color	Electro-optical characteristics (Ta=25°C)										Outline drawing
				V _F (V)		Condition I _F (mA)	I _R (μA)	Condition V _R (V)	I _V (mcd)	Condition I _F (mA)	λp	Δλ		
				typ	max								typ	
SEL1120R	 2x5	Red tinted, diffused	Red	2.0	2.5	10	50	3	0.7	10	700	100	Ⓐ	
SEL1420G	 2x5	Green tinted, diffused	Green						2.0	20	560	20		
SEL1720Y	 2x5	Yellow tinted, diffused	Yellow						0.7	10	570	40		
SEL1820D	 2x5	Orange tinted, diffused	Amber	2.0					610		35			
SEL1920D	 2x5	Orange tinted, diffused	Orange	0.7					587		33			
SEL1121R	 3x5	Red tinted, diffused	Red	2.0	2.5	10	50	3	0.7	10	700	100	Ⓑ	
SEL1421G	 3x5	Green tinted, diffused	Green						2.0	20	560	20		
SEL1721Y	 3x5	Yellow tinted, diffused	Yellow						0.7	10	570	40		
SEL1821D	 3x5	Orange tinted, diffused	Amber	1.5					610		35			
SEL1921D	 3x5	Orange tinted, diffused	Orange	0.7					587		33			
SEL1222R	 2.5x5	Red tinted, diffused	High intensity red	1.9	2.5	10	50	3	5.0	20	630	35	Ⓒ	
SEL1422G	 2.5x5	Green tinted, diffused	Green	2.0					4.0	10	560	20		
SEL1722Y	 2.5x5	Yellow tinted, diffused	Yellow						4.0		570	40		
SEL1822D	 2.5x5	Orange tinted, diffused	Amber						2.5		610	35		
SEL1922D	 2.5x5	Orange tinted, diffused	Orange	1.9					3.0		587	33		
SEL1124R	 1x4.9	Red tinted, diffused	Red	2.0	2.5	10	50	3	0.7	10	700	100	Ⓓ	
SEL1424G	 1x4.9	Green tinted, diffused	Green						2.0	20	560	20		
SEL1724Y	 1x4.9	Yellow tinted, diffused	Yellow						0.7	10	570	40		
SEL1824D	 1x4.9	Orange tinted, diffused	Amber	1.9					2.1		610	35		
SEL1924D	 1x4.9	Orange tinted, diffused	Orange						0.7		587	33		