



Wiha Sockets



713 Hex Sockets 1/4" Square drive socket. Replaceable bit. 1/4" bits CVM steel.

Item				
No.	Inch	mm	lbs.	
713 71	1/16	38	.05	
713 70	5/64	38	.05	
713 72	3/32	38	.05	
713 74	7/64	38	.05	
713 76	1/8	38	.05	
713 78	9/64	38	.05	
713 80	5/32	38	.05	
713 82	3/16	38	.05	
713 84	7/32	38	.05	
713 86	1/4	38	.05	



713 Hex Metric Sockets 3/8" Square drive socket. Replaceable bit. 1/4" bits CVM steel.

Item				
No.	mm	mm	lbs.	
713 00	2.0	42	.09	
713 16	2.5	42	.09	
713 41	3.0	42	.09	
713 31	4.0	42	.09	
713 23	5.0	42	.09	
713 25	6.0	42	.09	
713 20	8.0	42	.10	
713 22	10.0	42	.11	



721 Hex To Square 1/4" socket bit adapter.

Item					
No.	Size	mm	Drive	lbs.	
721 10	1/4"	25	1/4"	.03	
721 15	1/4"	30	3/8"	.05	



713 Hex Sockets 3/8" Square drive socket. Replaceable bit. 1/4" bits CVM tool steel.

Item				
No.	Inch	mm	lbs.	
713 75	1/8	42	.09	
713 77	9/64	42	.09	
713 79	5/32	42	.09	
713 81	3/16	42	.09	
713 83	7/32	42	.09	
713 85	1/4	42	.09	
713 88	5/16	42	.10	
713 90	3/8	42	.10	



713 Hex Metric Sockets 3/8" Square drive socket. Replaceable bit. 5/16" bits CVM steel.

Item				
No.	mm	mm	lbs.	
713 32	12.0	75	.22	



761 Security Hex Inch Sockets 3/8" Square drive socket. Replaceable bit. 1/4" bits CVM steel.

Item				
No.	Inch	mm	lbs.	
761 64	5/64	42	.09	
761 65	3/32	42	.09	
761 66	7/64	42	.09	
761 67	1/8	42	.09	
761 68	9/64	42	.09	
761 69	5/32	42	.09	
761 70	3/16	42	.09	
761 71	7/32	42	.09	
761 72	1/4	42	.09	



713 Hex Metric Sockets 1/4" Square drive socket. Replaceable bit. 1/4" bits CVM steel.

Item				
No.	mm	mm	lbs.	
713 01	1.5	38	.04	
713 02	2.0	38	.04	
713 05	2.5	38	.04	
713 13	3.0	38	.04	
713 14	4.0	38	.04	
713 17	5.0	38	.05	
713 19	6.0	38	.05	
713 27	8.0	38	.05	
713 40	10.0	38	.05	



720 Impact Bit Holding Socket With Retaining Ring For 1/4" drive bits.

Item					
No.	Bit	mm	Drive	lbs.	
720 01	1/4	25	1/4"	.05	
720 02	1/4	30	3/8"	.10	
720 03	1/4	35	1/2"	.21	



720 Impact Bit Holding Socket With Retaining Ring For 5/16" drive bits.

Item					
No.	Bit	mm	Drive	lbs.	
720 04	5/16	25	1/4"	.04	
720 05	5/16	30	3/8"	.04	
720 06	5/16	35	1/2"	.04	