

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0541225012
Status: Obsolete
Description: 1.27mm (.050") Pitch Wire-to-Board Shielded Receptacle, Vertical, Dual Row, 50 Circuits
Replacement Part Number: 541225029

Documents:
[Drawing \(PDF\)](#)

General

Product Family	I/O Connectors
Series	54122
Application	Wire-to-Board
Component Type	Receptacle
Product Name	Leaf Style Contact
Replacement Part Number	541225029
Type	N/A

Physical

Circuits (Loaded)	50
Circuits (maximum)	50
Durability (mating cycles max)	500
Lock to Mating Part	Yes
Material - Plating Mating	Gold
Material - Plating Termination	Tin-Lead
Orientation	Vertical
PC Tail Length	3.18mm (.125")
PCB Retention	None
PCB Thickness - Recommended	1.60mm (.063")
Packaging Type	Tray
Panel Mount	Yes
Pitch - Mating Interface	1.27mm (.050")
Plating min - Mating	0.305µm (12µ")
Plating min - Termination	1.016µm (40µ")
Polarized to Mating Part	Yes
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-55°C to +85°C
Termination Interface: Style	Through Hole
Wire Size AWG	N/A

Electrical

Current - Maximum per Contact	1A
Shielded	Yes
Voltage - Maximum	250V

Material Info

Reference - Drawing Numbers

Product Specification	PS-52986-002, PS-52986-018, PS-54122-002
-----------------------	--

EU RoHS
Not RoHS Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
54122Series

Mates With
54306 , [Link:52316](#)