





(1,00 mm) .0394"


FTM-125-02-L-DV



FTMH-116-02-L-DV-P



FTMH-111-02-F-DV-ES-A



SMT MICRO TERMINAL STRIPS

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?FTMH or www.samtec.com?FTMH

Insulator Material:
Black Liquid Crystal Polymer

Terminal Material:
Phosphor Bronze

Current Rating (FTMH/CLM):
2.8 A per pin
(1 pin powered per row)

Operating Temp Range:
-55°C to +125°C

Plating:
Sn or Au over
50µ" (1,27 µm) Ni
RoHS Compliant:
Yes

Processing:
Lead-Free Solderable:
Yes

-DV Lead Coplanarity:
(0,10 mm) .004" max
-DH Lead Coplanarity:
(0,10 mm) .004" max (05-25)
(0,15 mm) .006" max (26-50)

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality





ALSO AVAILABLE (MOQ Required)

- End shrouds with board locks
 - Molded end shrouds for 05 through 08 positions
 - Other platings
- Contact Samtec.

Note: Some lengths, styles and options are non-standard, non-returnable.


Mates with:
CLM, MLE




Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM


FTMH-122-02-F-DV-EC




FTMH-120-02-L-DV




FTMH-135-02-F-DH





FTM-125-02-L-DV



FTMH-128-03-L-DV-EP




FTMH, FTM SERIES

Flex Shroud
options availableLow Profile
(1,27 mm) .050"Surface
mountShrouded and
alignment pin
options availableROW
OPTION



-DV

= Dual Vertical


-DH

= Dual Horizontal
(FTMH only)


FTM



Shrouded options removed for clarity



-DV OPTION



-SA OPTION

FLEX SHROUD OPTIONS

(FTMH-DV only with
9 pins/row minimum)

-ES

= End Shroud

-EC

= End Shroud with Locking Clip
(Manual placement required)

-EP

= End Shroud with Guide Post
(Use only when mating with CLM)

FTM	
OPTION	C
-S	(7,00) .276
-SA	(4,00) .157

(FTM only)

-S

= End Shroud
(05 positions minimum).
Molded or press fit shroud at
Samtec's discretion
(See assembly print at
www.samtec.com?FTM
for dimensions)

-SA

= End Shroud with Alignment Pins
(05 through 46 positions)

FTM	
LEAD STYLE	D
-02	(1,91) .075
-03	(1,65) .065

OTHER
OPTIONS

-A

= Alignment Pin
(3 positions minimum)
Metal or plastic at Samtec discretion
(FTMH-DV only)

-K


= (2,50 mm) .098" DIA Polyimide
Film Pick & Place Pad
(FTMH-DH only)

-P

= Plastic Pick & Place Pad
(-DV only)
(6 positions minimum)

-TR

= Tape & Reel



-P OPTION

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: +1-800-SAMTEC-9 or +1-812-944-6733 SAMTEC NORTHERN CALIFORNIA • Tel: +1-408-395-5900 SAMTEC SOUTHERN CALIFORNIA • Tel: +1-800-726-8329
 SAMTEC SOUTH AMERICA • Tel: +55 31 3786 3227 SAMTEC UNITED KINGDOM • Tel: +44 01236 739292 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0
 SAMTEC FRANCE • Tel: +33 1 60 95 06 60 SAMTEC ITALY • Tel: +39 039 6890337 SAMTEC NORDIC/BALTIC • Tel: +46 8 4477280 SAMTEC BENELUX • Tel: +44 01236 739292
 SAMTEC ISRAEL • Tel: +972 3 7526600 SAMTEC INDIA • Tel: +91 80 3272 1612 SAMTEC ANZ • Tel: +613 9580 0683 SAMTEC SINGAPORE • Tel: +65 6745 5955 SAMTEC JAPAN • Tel: +81 45 475 1385
 SAMTEC SHANGHAI • Tel: +86 21 6083 3766 SAMTEC SHENZHEN • Tel: +86 755 83776780 SAMTEC TAIWAN • Tel: +886 2 2735 6109 SAMTEC HONG KONG • Tel: +852 26904658 SAMTEC KOREA • Tel: +82 31 717 5685